








Aluminium C-rails						
630		1600			3200	
						
339902/03	339904/05	339920/21/22/23 (asafstand : 75 mm)	339931/32/33 (asafstand : 75 mm)	339925/26/27 (asafstand : 125 mm)	339920/21/22/23 (asafstand : 75 mm)	339925/26/27 (asafstand : 125 mm)
XL ³ S 630						
339902/03 + 337979						
	339904/05 + 337980					
	339904/05 + 337981					
	339904/05 + 337982					
339902/03 + 337979 x 2 ⁽¹⁾						
339902/03 + 337980 x 2 ⁽¹⁾						
339902/03 + 337981 x 2 ⁽¹⁾						
339902/03 + 337982 x 2 ⁽¹⁾						
XL ³ S 4000						
		339920/23 + 339940 ⁽⁵⁾			339920 + 339923 + 339924 ⁽⁵⁾	
		339921/23 + 339940 ⁽⁵⁾		339925/27 + 339940 ⁽⁵⁾	339921 + 339923 + 339924 ⁽⁵⁾	339925 + 339927 + 339924 ⁽⁵⁾
		339921/23 + 339940 of 339920/23 + 339940 ⁽⁶⁾		339925/27 + 339940 ⁽⁵⁾	339921 + 339923 + 339924 of 339920 + 339923 + 339924 ⁽⁶⁾	339925 + 339927 + 339924 ⁽⁵⁾
		339922/23 + 339940 ⁽⁵⁾		339926/27 + 339940 ⁽⁵⁾	339922 + 339923 + 339924 ⁽⁵⁾	339926 + 339927 + 339924 ⁽⁵⁾
		339922/23 + 339940 of 339921/23 + 339940 ⁽⁶⁾		339926/27 + 339940 of 339925/27 + 339940 ⁽⁶⁾	339922 + 339923 + 339924 of 339921 + 339923 + 339924 ⁽⁶⁾	339926 + 339927 + 339924 of 339925 + 339927 + 339924 ⁽⁶⁾
		339920/23 + 339940 ⁽⁷⁾			339920 + 339923 + 339924 ⁽⁷⁾	
		339921/23 + 339940 ⁽⁷⁾		339925/27 + 339940 ⁽⁷⁾	339921 + 339923 + 339924 ⁽⁷⁾	339925 + 339927 + 339924 ⁽⁷⁾
		339921/23 + 339940 ⁽⁷⁾ of 339920/23 + 339940 ⁽⁸⁾		339925/27 + 339940 ⁽⁷⁾	339921 + 339923 + 339924 ⁽⁷⁾ of 339920 + 339923 + 339924 ⁽⁸⁾	339925 + 339927 + 339924 ⁽⁷⁾
		339922/23 + 339940 ⁽⁷⁾		339926/27 + 339940 ⁽⁷⁾	339922 + 339923 + 339924 ⁽⁷⁾	339926 + 339927 + 339924 ⁽⁷⁾
		339922/23 + 339940 ⁽⁷⁾ of 339921/23 + 339940 ⁽⁸⁾		339926/27 + 339940 ⁽⁷⁾ of 339925/27 + 339940 ⁽⁸⁾	339922 + 339923 + 339924 ⁽⁷⁾ of 339921 + 339923 + 339924 ⁽⁸⁾	339926 + 339927 + 339924 ⁽⁷⁾ of 339925 + 339927 + 339924 ⁽⁸⁾
339902/03 + 339734		339920/23 + 339940 ⁽⁴⁾				
339902/03 + 339735		339921/23 + 339940		339925/27 + 339940		
339902/03 + 339735		339921/23 + 339940		339925/27 + 339940		
339902/03 + 339736		339922/23 + 339940		339926/27 + 339940		
339902/03 + 339736		339922/23 + 339940		339926/27 + 339940		

6 : montage achter dwarssteun van centraal stijprofiel

7 : montage op dwarssteunen in de kast

8 : montage achter stijprofielen

9 : behalve diepte 400 mm ; 10 : de 2 samengestelde rails worden boven elkaar in de hoogte van de kast geplaatst ; 11 : 630 A max.