








Keuzetabel railstellen voor XL³ S 630 en XL³ S 4000

			≤ 400				≤ 800					
Railstelhouders voor platte rails			 339900 Railstelhouder verticaal		 339901 Railstelhouder horizontaal		 339906 Railstelhouder verticaal		 Railstelhouder horizontaal			
Ref.	Doorsnede (mm)	Aantal rails per fase	I (A)		I (A)		I (A)		I (A)		I (A)	
			IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30
037434	18 x 4	1	245	200	245	200	245	200	245	200	245	200
037438	25 x 4	1	280	250	280	250	-	-	-	-	-	-
037418	25 x 5	1	330	270	330	270	330	270	330	270	330	270
037419	32 x 5	1	450	400	450	400	450	400	450	400	450	400
037440	50 x 5	1	-	-	-	-	-	-	700	630	630	550
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-
037441	63 x 5	1	-	-	-	-	-	-	800	700	720	630
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-
037459	75 x 5	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-
037443	80 x 5	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-
037446	100 x 5	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-
	125 x 5	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
		4	-	-	-	-	-	-	-	-	-	-
	50 x 10	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
	60 x 10	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
	80 x 10	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
	100 x 10	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-
	120 x 10	1	-	-	-	-	-	-	-	-	-	-
		2	-	-	-	-	-	-	-	-	-	-
		3	-	-	-	-	-	-	-	-	-	-

			≤ 630				≤ 1600			
Railstelhouders voor aluminium C-rails			 339902/03 Railstelhouder verticaal		 339904/05 Railstelhouder horizontaal		 339931/32/33 (asafstand : 75 mm) Railstelhouder verticaal			
Ref.	Doorsnede (mm)	Aantal rails per fase	I (A)		I (A)		I (A)		I (A)	
			IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30
404430	187	1	320	250	320	250	320	250	-	-
404431	238	1	500	400	500	400	500	400	-	-
404432	323	1	700	630	700	630	700	630	-	-
037354	524	1	-	-	-	-	-	-	800	630
037355	549	1	-	-	-	-	-	-	1000	800
037356	586	1	-	-	-	-	-	-	1250	1000
037357	686	1	-	-	-	-	-	-	1450	1250
037358	824	1	-	-	-	-	-	-	1750	1600
037358 x 2	824 x 2	2	-	-	-	-	-	-	-	-

1 : een houder ref. 339920/21/22 en een houder ref. 339923 in combinatie

2 : een houder ref. 339925/26 en een houder ref. 339927 in combinatie