

XL³ S 630

deuren voor kasten



337641

337691

337682

337683

337791

337792

337793

Ref.	Metalen deuren voor behuizingen XL ³ S 630	
	Breedte 16 modules	
	Geleverd met vaste handgreep Cilinderslot afzonderlijk te bestellen 2 of 3 vergrendelingspunten (naargelang de hoogte van de deur) voor kasten met afdekbare hoogte (mm)	
337641	750	
337651	900	
337661	1050	
337671	1200	
337681	1350	
337691	1500	
337701	1650	
337711	1800	
337721	1950	
337731	2100	
337741	2250	
	Breedte 24 modules	
337642	750	
337652	900	
337662	1050	
337672	1200	
337682	1350	
337692	1500	
337702	1650	
337712	1800	
337722	1950	
337732	2100	
337742	2250	
	Breedte 36 modules	
337643	750	
337653	900	
337663	1050	
337673	1200	
337683	1350	
337693	1500	
337703	1650	
337713	1800	
337723	1950	
337733	2100	
337743	2250	

Ref.	Glazen deuren voor behuizingen XL ³ S 630	
	Breedte 16 modules	
	Geleverd met vaste handgreep Cilinderslot afzonderlijk te bestellen 2 of 3 bevestigingspunten (naargelang de hoogte van de deur) voor kasten met afdekbare hoogte (mm)	
337751	750	
337761	900	
337771	1050	
337781	1200	
337791	1350	
337801	1500	
337811	1650	
337821	1800	
337831	1950	
337841	2100	
337851	2250	
	Breedte 24 modules	
337752	750	
337762	900	
337772	1050	
337782	1200	
337792	1350	
337802	1500	
337812	1650	
337822	1800	
337832	1950	
337842	2100	
337852	2250	
	Breedte 36 modules	
337753	750	
337763	900	
337773	1050	
337783	1200	
337793	1350	
337803	1500	
337813	1650	
337823	1800	
337833	1950	
337843	2100	
337853	2250	

Software XL PRO³ borden
www.legrand.be > support



Vervangingshandgrepen voor deuren **blz. 276**