







KOPPELINGEN		AFTAKKINGEN		TOEBEHOREN		MOEREN
						
Elleboog 90°	Sokkels 90°	Voor buizen Ø binnen ⁽¹⁾	Y-vorming	Dichting IP 68	Voetstukken	Kunststof
UR ⁽²⁾⁽⁴⁾ goedgekeurd IMQ ⁽³⁾ goedgekeurd		IMQ ⁽³⁾ goedgekeurd		IMQ goedgekeurd		
Ref.	Ref.		Ref.	Ref.	Ref.	Ref.
666565	-	-	-	666959	666981	386671
666566	-	8 / 7 - 7	666938	666960	666982	386672
666568	-	12 / 8 - 8	666939	666962	666984	386672
666569	-	12 / 8 - 8	666939	666962	666984	386673
666570	-	15 / 8 - 8	666940	666963	666985	386673
666571	-	15 / 8 - 8	666941	666963	666985	386674
666573	-	19,5 / 15 - 15	666942	666965	666987	386674
666575	-	-	-	666967	666989	386675
-	666880	-	-	666969	666991	386676
-	666882	-	-	666971	666993	386677
666577	-	-	-	666959	666981	386661
-	-	-	-	666959	666981	386662
666578	-	8 / 7 - 7	666938	666960	666982	386661
666579	-	8 / 7 - 7	666938	666960	666982	386662
-	-	8 / 7 - 7	666938	666960	666982	386663
666582	-	12 / 8 - 8	666939	666962	666984	386663
666583	-	12 / 8 - 8	666939	666962	666984	386664
666584	-	15 / 8 - 8	666940	666963	666985	386664
666585	-	15 / 8 - 8	666941	666963	666985	386665
666588	-	19,5 / 15 - 15	666942	666965	666987	386665
666589	-	19,5 / 15 - 15	666942	666965	666987	386666
666591	-	-	-	666967	666989	386667
-	666880	-	-	666969	666991	386668
-	666882	-	-	666971	666993	386669
-	666882	-	-	666971	666993	386670