








## Flexibele buizen RTA in PVC met kunststof koppelingen

	PVC BUIS GE-PVC		PVC BUIS FP 2000		UNIVERSELE KOPPELING	MOEREN	Verwante koppelingen
							<b>GE-PVC buis + universele koppeling</b>
	Enkel		Verstevigd		Rechte mannelijke koppeling	Kunststof	
Binnen Ø(mm)	Ref.	Binnen Ø(mm)	Ref.	Draad	Ref.	Ref.	
<b>Voor draad ISO</b>							
10	387342	10	387560	ISO 16	382921	386672	
12	387343	12,5	387561	ISO 16	382922	386672	
				ISO 20	382923	386673	
15,5	387344	16	387562	ISO 20	382924	386673	
20,5	387345	21	387563	ISO 25	382925	386674	
27	387346	27	387564	ISO 32	382926	386675	
34,5	387347	35,5	387565	ISO 40	063609	386676	
39,5	387348	40,5	387566	ISO 40	382929	386676	
51	387350	52	387567	ISO 50	382997	386677	
<b>Voor draad PG</b>							
10	387342	10	387560	PG 9	382911	386662	
				-	-	-	
12	387343	12,5	387561	PG 11	382912	386663	
				PG 13,5	382913	386664	
15,5	387344	16	387562	PG 13,5	382914	386664	
				PG 16	382915	386665	
20,5	387345	21	387563	PG 21	382916	386666	
27	387346	27	387564	PG 29	382917	386667	
<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p><b>FP 2000 buis + Universele koppeling</b></p>  </div> <div style="text-align: center;"> <p><b>Metaal 2000 koppeling</b></p>  </div> </div>							
<p><b>FA of PN of P3 buis + Metaal 2000 koppeling</b></p> 