

P17 Tempra Pro IP 44 - LS 16 en 32 A

opbouwcontactdozen, half-inbouwcontactdozen, koppelstekkers, stekkers en toestelcontactdozen



555258



555184



555188



555108



555128



555214



555234 + 552127

Technische kenmerken zie www.ecatalog.be

Opbouwcontactdozen

Ref		IP 44		Twee mogelijke hoeken (5° of 25°)	
16 A	32 A	200/250 V~			
555154	555254	2P+A			
555155	555255	3P+A			
555156	555256	3P+N+A			
		380/415 V~			
555157	555257	2P+A			
555158	555258	3P+A			
555159	555259	3P+N+A			
		480/500 V~			
555162	555262	3P+A			
	555263	3P+N+A			

Half-inbouwcontactdozen met hartafstand 70 x 70 mm

Ref		IP 44		Geschikt voor bevestiging op volle of voorgeperforeerde afdekplaten (blz. 538) en op inbouwdozen (blz. 534)	
16 A	32 A	200/250 V~			
555184	555284	2P+A			
555185	555285	3P+A			
555186	555286	3P+N+A			
		380/415 V~			
555188	555288	3P+A			
555189	555289	3P+N+A			
		480/500 V~			
555192	555292	3P+A			

Half-inbouwcontactdozen met kleinere hartafstand

Ref		IP 44		Kunnen alleen op volle afdekplaten ref. 057715/16 worden bevestigd (blz. 538)	
16 A	32 A	200/250 V~			
057354	058054	2P+A			
		380/415 V~			
057358	058058	3P+A			
057359	058059	3P+N+A			

Half-inbouwcontactdozen met vergrendeling

Ref		IP 44		IP 55		16 A		Afmetingen : 125 x 105 mm Kunnen alleen op een afdekplaat ref. 057723 worden bevestigd (blz. 538)	
						200/250 V~			
057300	057320	2P+A							
		380/415 V~							
057302	057322	3P+N+A							

Koppelstekkers

Ref		IP 44		Vasttrekken van de kabel en sluiting zonder gereedschap Niet vergrendeld bij levering	
16 A	32 A	200/250 V~			
555104	555214	2P+A			
555105	555215	3P+A			
555106	555216	3P+N+A			
		380/415 V~			
555107	555217	2P+A			
555108	555218	3P+A			
555109	555219	3P+N+A			
		480/500 V~			
555112	555222	3P+A			
	555223	3P+N+A			

Rechte stekkers

Ref		IP 44		Vasttrekken van de kabel en sluiting zonder gereedschap Niet vergrendeld bij levering	
16 A	32 A	200/250 V~			
555124	555234	2P+A			
555125	555235	3P+A			
555126	555236	3P+N+A			
		380/415 V~			
555127	555237	2P+A			
555128	555238	3P+A			
555129	555239	3P+N+A			
		480/500 V~			
555132	555242	3P+A			
555133	555243	3P+N+A			

Fase-omschakelende stekkers

Ref		IP 44		Rechte stekkers waarmee de draairichting van een driefasige elektrische motor kan worden gewijzigd	
16 A	32 A	380/415 V~			
057440	058140	3P+A			
057441	058141	3P+N+A			

Toestelcontactdozen

Ref		IP 44		200/250 V~	
16 A	32 A				
057584	058284	2P+A			
057585		3P+A			
057586	058286	3P+N+A			
		380/415 V~			
057588	058288	3P+A			
057589	058289	3P+N+A			

Afsluitdoppen

Ref		Rubber		Voor stekkers en toestelcontactdozen	
052125		2P+A - 16 A			
052126		3P+A - 16 A			
052127		3P+N+A - 16 A / 2P+A en 3P+A - 32 A			
052799		3P+N+A - 32 A			