



Technische kenmerken zie www.ecatalog.be

Ref.	Opbouwcontactdozen	
	Twee mogelijke hoeken (5° of 25°)	
16 A	32 A	200/250 V~
555354	555454	2P+A
555355	555455	3P+A
555356	555456	3P+N+A
		380/415 V~
555358	555458	3P+A
555359	555459	3P+N+A
		480/500 V~
555362	555462	3P+A
Ref.	Half-inbouwcontactdozen	
	Kunnen op volle of voorgeperforeerde afdekplaten worden bevestigd (blz. 538)	
16 A	32 A	200/250 V~
555384	555484	2P+A
555385	555485	3P+A
555386	555486	3P+N+A
		380/415 V~
555388	555488	3P+A
555389	555489	3P+N+A
		480/500 V~
	555492	3P+A
Ref.	Koppelstekkers (IP 66/67/)	
	Niet vergrendeld bij levering	
16 A	32 A	200/250 V~
555304	555414	2P+A
555305	555415	3P+A
555306	555416	3P+N+A
		380/415 V~
555308	555418	3P+A
555309	555419	3P+N+A
		480/500 V~
	555422	3P+A
Ref.	Rechte stekkers (IP 66/67/)	
	Niet vergrendeld bij levering	
16 A	32 A	200/250 V~
555324	555434	2P+A
555325	555435	3P+A
555326	555436	3P+N+A
		380/415 V~
555328	555438	3P+A
555329	555439	3P+N+A
		480/500 V~
555332	555442	3P+A
Ref.	Toestelcontactdozen	
	Niet vergrendeld bij levering	
16 A	32 A	200/250 V~
056803	056823	2P+A
056804		3P+A
		380/415 V~
056807	056827	3P+A
056808	056828	3P+N+A



Ref.	Opbouwcontactdozen	
63 A	125 A	200/250 V~
555554		2P+A
555555		3P+A
555556		3P+N+A
		380/415 V~
555558	555658	3P+A
555559	555659	3P+N+A
Ref.	Half-inbouwcontactdozen	
	Kunnen bevestigd worden op frontplaten Ref. 057717/19 (blz. 538)	
63 A	125 A	200/250 V~
555584		2P+A
555585		3P+A
555586		3P+N+A
		380/415 V~
555588	555688	3P+A
555589	555689	3P+N+A
Ref.	Koppelstekkers (IP 66/67/69)	
	Niet vergrendeld bij levering	
63 A	125 A	200/250 V~
555504		2P+A
555505		3P+A
555506		3P+N+A
		380/415 V~
555508	555608	3P+A
555509	555609	3P+N+A
Ref.	Rechte stekkers (IP 66/67/69)	
	Niet vergrendeld bij levering	
63 A	125 A	200/250 V~
555524		2P+A
555525		3P+A
555526		3P+N+A
		380/415 V~
555528	555628	3P+A
555529	555629	3P+N+A
Ref.	Toestelcontactdozen	
	Niet vergrendeld bij levering	
63 A	125 A	200/250 V~
555514		2P+A
		380/415 V~
555518	555618	3P+A
555519	555619	3P+N+A