


2-draadsysteem - afmetingen


buitenposten Sfera New en Sfera Robur

■ Sfera New Inbouwdozen




Afmetingen			
Ref.	A	B	C
350010	117	123	45
350020	117	214	45
350030	117	306	45

■ Sfera Robur Inbouwdozen antivandalisme




Afmetingen			
Ref.	A	B	C
350110	102	114	51
350120	102	206	51
350130	102	297	51

■ Sfera New en Sfera Robur Opbouwdozen met regenbescherming



Afmetingen			
Ref.	A	B	C
350611	151	151	82
350612	151	151	82
350613	151	151	82
350621	151	242	82
350622	151	242	82
350623	151	242	82
350631	151	334	82
350632	151	334	82
350633	151	334	82
350641	290	242	82
350642	290	242	82
350643	290	242	82
350661	290	334	82
350662	290	334	82
350663	290	334	82
350691	429	334	82
350692	429	334	82
350693	429	334	82

■ Sfera New Regenbescherming



Afmetingen			
Ref.	A	B	C
350511	151	151	51
350512	151	151	51
350513	151	151	51
350521	151	242	51
350522	151	242	51
350523	151	242	51
350531	151	334	51
350532	151	334	51
350533	151	334	51
350541	290	242	51
350442	290	242	51
350543	290	242	51
350661	290	334	51
350562	290	334	51
350563	290	334	51
350691	430	334	51
350592	430	334	51
350593	430	334	51