





Keuzetabel kabelgoot P31+ RAL7021 (antraciet zwart)

hoogte 60 mm



Breedte in mm	KABELGOOT		SCHEIDINGSSCHOT	HULPSTUKKEN	
	Automatische koppeling	Automatische koppeling	scheidingschot L3000mm	Bochtstuk 90°	Aftakstuk
	P31+ MF Auto geperforeerd	P31+ MF Auto blind			
	 L=3	 L=3	 L=3		
100	VG480111-R7021	VG481121-R7021	VG481429 (sendzimir)	VG480751-R7021	VG481781-R7021
200	VG480113-R7021	VG481123-R7021		VG480753-R7021	VG481783-R7021
300	VG480114-R7021	VG481124-R7021		VG480754-R7021	VG481784-R7021
400	VG480115-R7021	VG481125-R7021		VG480755-R7021	VG481785-R7021
Bevestigen met kabelgoot				≤ 300 mm 4 x  M6 x 10 mm	≤ 300 mm 6 x  M6 x 10 mm
				≥ 400 mm 6 x  M6 x 10 mm	≥ 400 mm 9 x  M6 x 10 mm

Breedte in mm	DRAADSTANGOPHANGINGEN				
	Open C beugel	Inschuifbeugel	Plafondbeugel (ook voor schuin plafond)	Draadstang M10 L2000mm	Zeskantmoer M10
		 600 N	 750 N	 Max. 1500 N	 5800 N
100	VG347280-R7021	VG341280	8232010	8234110	8200310
200	VG347282-R7021	VG341282			
300	VG347283-R7021	VG341283			
400	VG347284-R7021	VG341284			

(1) finish is verzinkt zwart (niet gepoedercoat)