


VLOERMONTAGE												
Type	Breedte	Draadgoot		Montage- beugel UC 50	Universele beugel CM 50 XL	Bevestiging FTX	Verhoging R15	Verhoging R25	Verhoging R35	Verhoging R50	Verhoging R15/300	Montage- profiel RCSN
CF 54	50 mm	CM000061	EZ	CM586040		CM586180						
	100 mm	CM000071	EZ		CM586130	CM586180	CM586170	CM586640	CM586650	CM348530		CM013150
	150 mm	CM000081	EZ		CM586130	CM586180	CM586170	CM586640	CM586650	CM348530		CM013150
	200 mm	CM000091	EZ		CM586130	CM586180	CM586170	CM586640	CM586650	CM348530		CM013200
	300 mm	CM000101	EZ		CM586130					CM348530	CM586610	CM013300
	400 mm	CM000201	EZ							CM348530	CM586610	CM013400
	500 mm	CM000301	EZ							CM348530	CM586610	CM013500
	600 mm	CM000401	EZ							CM348530	CM586610	CM013600
CF 30	50 mm	CM000011	EZ	CM586040		CM586180						
	100 mm	CM000021	EZ		CM586130	CM586180	CM586170	CM586640	CM586650	CM348530		CM013150
	150 mm	CM000031	EZ		CM586130	CM586180	CM586170	CM586640	CM586650	CM348530		CM013150
	200 mm	CM000041	EZ		CM586130	CM586180	CM586170	CM586640	CM586650	CM348530		CM013200
	300 mm	CM000051	EZ		CM586130					CM348530	CM586610	CM013300
	400 mm	CM000801	EZ							CM348530	CM586610	CM013400
	500 mm	CM000811	EZ							CM348530	CM586610	CM013500
	600 mm	CM000851	EZ							CM348530	CM586610	CM013600
CF 105	100 mm	CM000891	EZ		CM586130		CM586170	CM586640	CM586650	CM348530		CM013150
	150 mm	CM000901	EZ		CM586130		CM586170	CM586640	CM586650	CM348530		CM013150
	200 mm	CM000911	EZ		CM586130		CM586170	CM586640	CM586650	CM348530		CM013200
	300 mm	CM000921	EZ		CM586130					CM348530	CM586610	CM013300
	400 mm	CM000931	EZ							CM348530	CM586610	CM013400
	500 mm	CM000941	EZ							CM348530	CM586610	CM013500
600 mm	CM001031	EZ							CM348530	CM586610	CM013600	

 Overige draadgoten **blz. 866**

 Koppelingen **blz. 868**



 Dekfels en scheidingsschotten **blz. 871**



 Wijze van installeren **blz. 876**