

| Binnenbocht | Buitenbocht | T-stuk | Stijg-/vervalstuk | Verloop-/eindplaat | Lengte 795 mm | Breedte |
|-------------|-------------|---------|-------------------|--------------------|---------------|---------|
| | | | | | | |
| 8312212 | 8312222 | 8312232 | 8312252 | VG350009 | 200 mm | |
| 8312213 | 8312223 | 8312233 | 8312253 | | 300 mm | |
| 8312214 | 8312224 | 8312234 | 8312254 | | 400 mm | |
| 8312215 | 8312225 | 8312235 | 8312255 | | 500 mm | |
| 8312216 | 8312226 | 8312236 | 8312256 | | 600 mm | |
| 8x | 8x | 12x | 8x | 4x | | |

| P31+ H = 25 mm als scheidingsgoot | | | Universele aanzetbocht | Montageplaat universeel | Breedte |
|------------------------------------|----------------|----------------|------------------------|-------------------------|--------------|
| Breedte 75 mm | Breedte 100 mm | Breedte 200 mm | | | |
| | | | | | |
| VG480045 | VG480046 | VG480048 | 8312290 | 8235200 | 200 - 600 mm |
| Bevestigen met Colring kabelbanden | | | 4x | 2x | |

Toepassing montageplaat steekverbinding

