

Binnenbocht	Buitenbocht	Aftakstuk	T-stuk	Stijg-/vervalstuk	Verloop-/eindplaat	Lengte 795 mm	Breedte
8312412	8312422	8312612	8312432	8312452	VG341161		200 mm
8312413	8312423	8312613	8312433	8312453			300 mm
8312414	8312424	8312614	8312434	8312454			400 mm
8312415	8312425	8312615	8312435	8312455			500 mm
8312416	8312426	8312616	8312436	8312456			600 mm
4x	4x	4x	6x	4x	2x		

P31+ H = 25 mm als scheidingsgoot			Universele aanzetbocht	Klemmontageplaat	Montageplaat universeel	Montageplaat horizontaal ⁽⁴⁾	Breedte
Breedte 75 mm	Breedte 100 mm	Breedte 200 mm					
VG480045	VG480046	VG480048	8312490	8312010	8235200	8312020	200 - 600 mm
Bevestigen met Colring kabelbanden			2x		2x		

Toepassing montageplaat steekverbinding



Ophangsystemen (blz. 894)

Colring kabelbanden (zie www.ecatalog.be)