

Binnenbocht	Buitenbocht	T-stuk	Stijg-/vervalstuk	Verloop-/eindplaat	Lengte 795 mm	Breedte
8312512	8312522	8312532	8312552	VG350009	200 mm	
8312513	8312523	8312533	8312553		300 mm	
8312514	8312524	8312534	8312554		400 mm	
8312515	8312525	8312535	8312555		500 mm	
8312516	8312526	8312536	8312556		600 mm	
8x	8x	12x	8x	4x		

P31+ H = 25 mm als scheidingsgoot			Universele aanzetbocht	Montageplaat universeel	Breedte
Breedte 75 mm	Breedte 100 mm	Breedte 200 mm	8312590	8235200	200 - 600 mm
VG480045	VG480046	VG480048			
Bevestigen met Colring kabelbanden			4x	2x	

### Toepassing montageplaat steekverbinding

