

| Binnenbocht | Buitenbocht                   | T-stuk                        | Stijg-/vervalstuk             | Verloopeindplaat | Breedte |
|-------------|-------------------------------|-------------------------------|-------------------------------|------------------|---------|
|             |                               |                               |                               |                  |         |
| 8362412     | 8362422                       | 8362432                       | 8362452                       | VG343161         | 200 mm  |
| 8362413     | 8362423                       | 8362433                       | 8362453                       |                  | 300 mm  |
| 8362414     | 8362424                       | 8362434                       | 8362454                       |                  | 400 mm  |
| 8362415     | 8362425                       | 8362435                       | 8362455                       |                  | 500 mm  |
| 8362416     | 8362426                       | 8362436                       | 8362456                       |                  | 600 mm  |
| 4x          | 4x  M6 x 12 mm <sup>(2)</sup> | 6x  M6 x 12 mm <sup>(2)</sup> | 4x  M6 x 12 mm <sup>(2)</sup> | 2x               |         |

| Koppelset instelbaar | Scheidingsschot L | Montageplaat universeel | Montageplaat horizontaal <sup>(3)</sup> | Breedte      |
|----------------------|-------------------|-------------------------|---|--------------|
|                      |                   |                         |   |              |
| 8363150              | CM923013          | VG350156                | 8362020                                 | 200 - 600 mm |
|                      | 4x                | 2x                      |   |              |