






























## Keuzetabel scheepsladder Van Geel SLB

H = 30 mm

Breedte in mm	Scheepsladder		Bochtstuk	Stijg-/vervalstuk	T-stuk	Aftakstuk
						
	Sportafstand 250 mm Lengte 3000 mm					
75 	0502-0753		0505-0075	0508-0075	0517-0075	0520-0075
100 	0502-1003		0505-0100	0508-0100	0517-0100	0520-0100
150 	0502-1503		0505-0150	0508-0150	0517-0150	0520-0150
200 	0502-2003		0505-0200	0508-0200	0517-0200	0520-0200
300 	0502-3003		0505-0300	0508-0300	0517-0300	0520-0300
400 	0502-4003		0505-0400	0508-0400	0517-0400	0520-0400
500 	0502-5003		0505-0500	0508-0500	0517-0500	0520-0500
Bevestigingsmaterialen	2x  <sup>(1)</sup>		4x  <sup>(1)</sup>	4x  <sup>(1)</sup>	6x  <sup>(1)</sup>	4x  <sup>(1)</sup>













(1) Universele verbinder: Ref. 0511-0100

(2) Zeskantbout M6 x 20 + sluitring M6 + zeskantmoer M6: Ref. 8069918 + 8363031 + 8069908

Breedte in mm	Scheepsladder	Bochtstuk	Stijg-/vervalstuk	T-stuk	Aftakstuk	
75 	0503-0753		0506-0075	0518-0075	0521-0075	
100 	0503-1003		0506-0100	0518-0100	0521-0100	
150 	0503-1503		0506-0150	0518-0150	0521-0150	
200 	0503-2003		0506-0200	0518-0200	0521-0200	
300 	0503-3003		0506-0300	0518-0300	0521-0300	
400 	0503-4003		0506-0400	0518-0400	0521-0400	
500 	0503-5003		0506-0500	0518-0500	0521-0500	
Bevestigingsmaterialen	2x  <sup>(1)</sup>		4x  <sup>(1)</sup>	4x  <sup>(1)</sup>	6x  <sup>(1)</sup>	4x  <sup>(1)</sup>

(1) Universele verbinder: Ref. 0512-0100

(2) Zeskantbout M6 x 20 + sluitring M6 + zeskantmoer M6: Ref. 8069918 + 8363031 + 8069908

Breedte in mm	Scheepsladder	Bochtstuk	Stijg-/vervalstuk	T-stuk	Aftakstuk	
75 	4501-0753		4505-0075	4508-0075	4517-0075	
100 	4501-1003		4505-0100	4508-0100	4517-0100	
150 	4501-1503		4505-0150	4508-0150	4517-0150	
200 	4501-2003		4505-0200	4508-0200	4517-0200	
300 	4501-3003		4505-0300	4508-0300	4517-0300	
400 	4501-4003		4505-0400	4508-0400	4517-0400	
500 	4501-5003		4505-0500	4508-0500	4517-0500	
Bevestigingsmaterialen	2x  <sup>(1)</sup>		4x  <sup>(1)</sup>	4x  <sup>(1)</sup>	6x  <sup>(1)</sup>	4x  <sup>(1)</sup>

(1) Universele verbinder: Ref. 4511-0100

(2) Zeskantbout M6 x 20 + sluitring M6 + zeskantmoer M6: Ref. CM801304 + 8049929 + 8049908