

Steunen en profielen universeel

Momentopname > Belasting >	Steunen & profielen					
	R21S		P21S		U50	
	Ophangrail		Plafondsteun		Plafondsteun	
	Licht		Licht		Middelzwaar	
	120 Nm		90 Nm		210 Nm	
	2.000 N		14.000 N		7.000 N	
Lengte in mm						
200	VG348042	VG348342	VG348139	VG348092	VG348362	VG348382
300	VG348043	VG348343	VG348140	VG348093	VG348363	VG348383
400	VG348044	VG348344	VG348141	VG348094	VG348364	VG348384
500	VG348045	VG348345	VG348142	VG348095	VG348365	VG348385
600	VG348046	VG348346	VG348143	VG348096	VG348366	VG348386
700	VG348047	VG348347	VG348144	VG348097	VG348367	VG348387
800			VG348145	VG348098	VG348368	VG348388
900			VG348147	VG348099	VG348369	VG348389
1000	VG348040	VG348340	VG348146	VG348090	VG348360	VG348390
1100				VG348091	VG348371	VG348391
1200			VG348148	VG348089	VG348372	VG348392
1300						VG348393
1400						VG348394
1500						VG348395
1600						VG348397
1800						VG348381
2000						VG348396
Incl. beschermkap	Nee	Nee	Nee	Nee	Nee	Nee

	R21S profiel dikte: 1,5 mm		R41S profiel dikte: 2,5 mm		U60 profiel	I-80 profiel
Lengte in mm						
2000	VG348041	VG348341				
3000	VG342180	VG342183	VG345200	VG345203	VG348378	8766730
4500					VG348379	
6000						8766760
Toe te passen consoles	Console licht 800 tot 1500 N		Console middelzwaar 1500 N		Console zwaar 3000 / 6000 N	(Klem)console extra zwaar 6000N + consolehaak (klem)