

Bevestigingsmateriaal

Toepassing							
P31+ kabelgoot	Cablofil draadgoot	SSL kabelbaan	GLO-4 kabelladder	SLB scheepsladder	Swifts industriële kabelladder	Draadstangophanging	R21/R41/P21S/U-50/U-55/U-60
SDZ	SDZ	SDZ	SDZ			SDZ	SDZ
THVZ	THVZ	THVZ	THVZ	THVZ	THVZ	THVZ	THVZ
RVS	RVS	RVS		RVS	RVS	RVS	

	Ø mm	lengte mm													
Multiclip							VG349252	✓						✓	✓
Zeskantmoer															
Zeskantmoer M6	M6		8019908		8069908		8049908	✓	✓		✓	✓		✓	
Zeskantmoer M8	M8		8313060		8069907		8049907	✓	✓		✓	✓		✓	✓
Zeskantmoer M10	M10		8200300		8069906		8049906	✓	✓		✓	✓	✓	✓	✓
Zeskantmoer M12	M12		8238300				CM801634		✓				✓		
Kraagmoer															
Kraagmoer M6	M6		8200200		8069915		CM801204	✓	✓	✓	✓	✓			
Kraagmoer M8	M8		CM801211												
Kraagmoer M10	M10		CM801221								✓	✓			
Kraagschroef															
Kraagschroef M6 x 10	M6	10	8200100					✓		✓	✓				
Kraagschroef + kraagmoer	M6	10	8200102					✓		✓	✓				
Slotbout															
Slotbout M8x16	M8	16	8713071												✓
Slotbout M8x25	M8	16													✓
Slotbout M8x35	M8	35	8313070		8069941										✓
Slotbout M10x25	M10	25			8069935		8049912				✓	✓			✓
Slotbout + kraagmoer															
Slotbout+kraagmoer M6 x 10	M6	10					VG346895	✓							
Slotbout+kraagmoer M6 x 12	M6	12	CM801001		CM350401		CM801004	✓	✓						
Slotbout+kraagmoer M6 x 20	M6	20	CM801011		CM350402		CM801014		✓						
Slotbout+kraagmoer M6 x 30	M6	30	CM801021						✓						
Slotbout+kraagmoer M10 x 20	M10	20			LFGM10		LFSM10				✓	✓			
Sluistring															
Sluistring M6	M6		8200800		8363031		8049929	✓	✓		✓	✓		✓	
Sluistring M8 (8,4 x 20 x 1,5)	M8	20	8313029				8049910	✓	✓		✓			✓	
Sluistring M8 (8,4 x 25 x 2)	M8	25	8313030		8069943				✓					✓	✓
Sluistring M10 (10,5 x 21 x 2)	M10	21	8200400		8069909		8049909		✓		✓	✓	✓	✓	✓
Sluistring M10 (10,5 x 30 x 2,5)	M10	30	8313090		8069946				✓					✓	
Sluistring M10 (10,5 x 40 x 2,5)			8313095						✓						
Sluistring M12	M12		CM801531				CM801534		✓				✓		