



Toepassing							
P31+ kabelgoot	Cablofil draadgoot	SSL kabelbaan	GLO-4 kabeladder	SLB scheeps ladder	Swifts industriële kabeladder	Draadstangophanging	R21/R41/P21S/U-50/U-55/U-60
SDZ	SDZ	SDZ	SDZ			SDZ	SDZ
THVZ	THVZ	THVZ	THVZ	THVZ	THVZ	THVZ	THVZ
RVS	RVS	RVS		RVS	RVS	RVS	

								RVS 316	ZnNi THVZ	SEND EZ	lengte mm	Ø mm	
												<b>Draadstang</b>	
	✓					✓	CM801704	VG350456			1000	M6	Draadstang M6 (3000N)
	✓		✓			✓	CM801714	VG350457	8234008		1000	M8	Draadstang M8 (3000N)
	✓		✓		✓	✓	4192-0100	VG350458	8234000		1000	M10	Draadstang M10 (5800N)
	✓					✓		VG350459	8238000		1000	M12	Draadstang M12
	✓		✓			✓			8234108		2000	M8	Draadstang M8 (3000N)
	✓		✓			✓			8234100		2000	M10	Draadstang M10 (5800N)
	✓					✓			8234206		3000	M6	Draadstang M6 (3000N)
	✓		✓			✓			8234208		3000	M8	Draadstang M8 (3000N)
	✓		✓			✓			8234200		3000	M10	Draadstang M10 (5800N)
	✓		✓										<b>Zeskantbout</b>
				✓	✓						12	M6	Zeskantbout M6 x 12
											20	M6	Zeskantbout M6 x 20
	✓					✓	CM801324	8069903			20	M8	Zeskantbout M8 x 20
	✓					✓			8313020		20	M8	Zeskantbout M8 x 25
	✓						8049936		CM801341		40	M8	Zeskantbout M8 x 40
	✓			✓	✓	✓	8049952	8069920	CM801361		20	M10	Zeskantbout M10 x 20
											30	M10	Zeskantbout M10 x 30
											80	M10	Zeskantbout M10 x 80
	✓						CM801404		CM801401		25	M12	Zeskantbout M12 x 25
													<b>Verlengnippel</b>
	✓		✓			✓		VG350431	8234508		30	M8	Verlengnippel M8 x 30
	✓		✓			✓		VG350432	8234500		30	M10	Verlengnippel M10 x 30
						✓		VG350433	8238500		36	M12	Verlengnippel M12 x 36
						✓							
						✓					8237200	M10	<b>Schuifmoer</b>
						✓					8313010	M8	<b>Ankermoer</b>
	✓										CM801211	M8	<b>Kartelmoer</b>
						✓					8233200	M10	<b>Oogbout</b>
			✓								8313000	M5	<b>Glijmoer</b>
													<b>Bevestigingsset</b>
				✓	✓		LFCOVSM6	LFCOVGM6				M6	Bevest. set dekseloverlap M6
		✓			✓		LFDVSM6	LFDVGM6				M6	Bevest. set scheid.schot M6