

Keuzetabel E30 - E90 constructies

technische kenmerken (vervolg)

E30 - E90 constructies (vervolg)							
Profiel R21S ⁽²⁾ (41 x 21 x1,5)	Console CB	Console CRP zwaar	Steun U55	Bevestigings- hoek voor draadstang	Draadstang M10 Lengte 1000 mm Elvz	Plafondbeugel	Breedte in mm
-	-	-	-	-	-	-	100 mm
-	-	-	-	-	-	-	200 mm
-	-	-	-	-	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	-	100 mm
-	-	-	-	-	-	-	200 mm
VG348042	-	-	-	-	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	8238700 (optioneel)	100 mm
VG348043	-	-	-	150 mm			
VG348043	-	-	-	200 mm			
VG348044	-	-	-	300 mm			
VG348045	-	-	-	400 mm			
-	VG350810	-	-	VG350122	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	8238700 (optioneel)	100 mm
-	VG350820	-	-				150 mm
-	VG350830	-	-				200 mm
-	VG350840	-	-				300 mm
-	VG350850	-	-				400 mm
-	VG350810	-	VG348362 - L = 200 mm VG348363 - L = 300 mm VG348364 - L = 400 mm VG348365 - L = 500 mm VG348366 - L = 600 mm VG348367 - L = 700 mm VG348368 - L = 800 mm VG348369 - L = 900 mm VG348360 - L = 1000 mm VG348371 - L = 1100 mm VG348372 - L = 1200 mm	VG350122	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	-	100 mm
-	VG350820	-	-				150 mm
-	VG350830	-	-				200 mm
-	VG350840	-	-				300 mm
-	VG350850	-	-				400 mm
-	-	CM557213	-	-	-	-	100 mm
-	-	CM557233	-	-	-	-	150 mm
-	-		-	-	-	-	200 mm
4x M10 ⁽¹⁾	2x M6 x 10 mm ⁽¹⁾	-	2x M6 x 10 mm ⁽¹⁾ voor draadstang	1x M6 x 10 mm ⁽¹⁾ voor draadstang	-	-	Bevestigings- materialen
-	Wand M8 ⁽⁶⁾	-	Plafond : 2 x M10 ⁽⁴⁾ M8 ⁽⁵⁾ Console : 1 x M8 ⁽⁵⁾	-	 M10 ⁽⁶⁾	-	Montage- materialen

Bevestigingshoek: te bevestigen aan de zijwand van de P31+kabelgoot. Vastzetten met kraagmoer en 2 x kraagschroef M6 x 10mm

