















E30 - E90 constructies

Profiel R21SP (41x21 mm)	Steun U55	Console middelzwaar 1500 N	Afsteunprofiel	Consoleklem ZnMg	Wandbeugel 2 per 1200 mm	Kabelklem FB thermisch verzinkt
						
VG348049	-	-	-	VG344872	-	-
VG348049	-	-	-	VG344872	-	-
-	VG348362 t/m VG348372 (zie blz. 947)	8717220	8238801	VG344872	-	-
-	-	8717230	-	-	-	-
-	-	8717240	-	-	-	-
-	-	8717220	8238801	VG344872	-	-
-	-	8717230	-	-	-	-
-	-	8717240	-	-	-	-
-	-	-	-	-	8313160	8190200 t/m 8190211 (zie blz. 946)
-	-	2x  M6 x 10 mm ⁽¹⁾	2x  M6 x 10 mm ⁽¹⁾	1x  M6 x 10 mm ⁽¹⁾	2x  M6 x 10 mm ⁽¹⁾	-
-	Plafond : 2x  M10 ⁽³⁾	Muur/wand : 1x  M10 ⁽⁵⁾	-	-	1x  M8 ⁽⁶⁾	-