

# Lijsten en wandgoten in PC ABS - halogeen vrij

keuzetabel

Doorsnede in mm		Lijsten voor distributie, wit			Wandgoten, wit				
		25 x 25	25 x 40	40 x 60	50 x 85	50 x 100 <sup>(1)</sup>	50 x 130	50 x 190	
Configuratie									
VOLLEDIGE LIJSTEN/WANDGOTEN	Wandgoot (2 m) + deksel (2 m)	637100	637110	637120	611707	611710	611708	611709	
	Scheidingstussenschot (2 m)	-	-	-	611706	611706	611706	611706	
AFWERKINGS-TOEBEHOREN	Einddeksel	637104	637114	637314	611741	638035	611743	611745	
	Binnenhoek	637101	637111	637311	611731	638031	611733	611735	
	Buitenhoek	637102	637112	637312	611721	638032	611723	611725	
	Platte hoek	637103	637113	637313	611711	638033	611713	611715	
	T-aftakking	637106	637116	637316	-	-	638034	-	
	Profielafdichting	-	-	-	611751	638036	611753	611755	
	Dekselafdichting	637105	637115	637315	611796	611796	611796	611796	
MONTAGE APPARATUUR	Mosaic opklikbare houder	Enkel (2 modules)	-	-	-	611797	611797	611797	611797
		Dubbel (4 modules)	-	-	-	611798	611798	611798	611798
		Drievoudig (6 modules)	-	-	-	611799	611799	611799	611799
	Contactdozen te klikken in de houders (hierboven)	Enkel 1 x 2P+A	-	-	-	077145L	077145L	077145L	077145L
		Dubbel 2 x 2P+A	-	-	-	077142L	077142L	077142L	077142L
		Drievoudig 2 x 2P+A	-	-	-	077143L	077143L	077143L	077143L
	Andere apparatuur	Houder 1 mechanisme	-	-	-	611788	611788	611788	611788
		Isolatie doos	-	-	-	611789	611789	611789	611789

