

CERTIFICATE FI/42479 Issue 2

Our Ref. HEL-CERT210100070-27



Product Range of enclosures
Type CUBO O-series (OPCP,OPCM)
Trademark ENSTO

Certificate Holder Legrand Finland Oy
Ensio Miettisen katu 2,
FI-06100 Porvoo, Finland

Technical information Degree of protection (EN 60529) IP66 / IP67
Mechanical strength (EN 62262) IK08 +35 °C / -25 °C
Static loads mounting plate 2 kg / dm²
Rated voltage 1000 V a.c. / 1500 V d.c.

Other information Empty enclosure for wall mounting
Material: Polycarbonate
Intended location: Outdoor & indoor

The product is certified according to the following standard(s) EN IEC 62208:2023

Validity This certificate is valid until 2031-03-31 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Date of issue 2026-03-31

SGS Fimko Oy

Signature


Joonas Leinonen
Certification Manager



Manufacturer

Legrand Finland Oy
Ensio Miettisen katu 2,
FI-06100 Porvoo, Finland

Manufacturing site

Legrand Estonia OÜ
Keki 1
EE-76606 Keila, Estonia

Additional information

The serie includes the following types:

Type	size (mm)	Type	size (mm)
OPCP 202013 G/T	200 x 200 x 132	OPCP 202018 G/T	200 x 200 x 187
OPCP 203013 G/T	200 x 300 x 132	OPCP 203018 G/T	200 x 300 x 187
OPCP 204013 G/T	200 x 400 x 132	OPCP 204018 G/T	200 x 400 x 187
OPCP 303013 G/T	300 x 300 x 132	OPCP 303018 G/T	300 x 300 x 187
OPCP 304013 G/T	300 x 400 x 132	OPCP 304018 G/T	300 x 400 x 187
OPCP 306013 G/T	300 x 600 x 132	OPCP 306018 G/T	300 x 600 x 187
OPCP 404013 G/T	400 x 400 x 132	OPCP 404018 G/T	400 x 400 x 187
OPCP 406013 G/T	400 x 600 x 132	OPCP 406018 G/T	400 x 600 x 187
OPCM 303013 G/T	300 x 300 x 132	OPCM 303018 G/T	300 x 300 x 187
OPCM 304013 G/T	300 x 400 x 132	OPCM 304018 G/T	300 x 400 x 187
OPCM 306013 G/T	300 x 600 x 132	OPCM 306018 G/T	300 x 600 x 187

...G grey cover
...T transparent cover
...M... metric knockouts

The models OPCP....018 G/T and OPCM....018 G/T are assembled by adding an extension frame(55 mm) to the OPCF....013 G/T and OPCM....013 G/T models.

This certificate replaces previous certificate no FI/42479 Issue 1, dated 2026-01-28 due to new testing

As shown in the Test Report(s) No(s): HELES2510000831-1