

CERTIFICATE FI/40945

Our Ref. HEL-CERT210100070-07



Product	Range of enclosures	
Type	CUBO O- series (OABP)	
Trademark	E or ENSTO	
Certificate Holder	Ensto Building Systems Finland Oy Ensio Miettisen katu 2 FI-06150, Porvoo, Finland	
Technical information	Degree of protection (EN 60529)	IP66 / IP67
	Mechanical strength (EN 62262)	IK08 +35 °C / IK07 -25 °C
	Static loads	mounting plate 2 kg / dm ²
	Rated voltage	1000 V a.c. / 1500 V d.c.
Other information	Material ABS Empty enclosure The series includes following types, see page 2 of this Certificate	
The product is certified according to the following standard(s)	EN 62208:2011	

Validity This certificate is valid until 09 February 2026 provided that the Conditions for FI certification are met. This certificate includes the right to use the FI mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for FI certification are met.

Date of issue 09 February 2021

SGS Fimko Ltd

Signature



Sixten Löfkors
Project Manager



Manufacturer Ensto Building Systems Finland Oy
 Ensio Miittisen katu 2
 FI-06150, Porvoo, Finland

Manufacturing site Ensto Building Systems Oü
 Keki 1
 EE-76606, Keila, Estonia

Directive information The certified product(s) fulfils requirements of mentioned standard(s) which are harmonised under the Low Voltage Directive (2014/35/EU) at the date of issue of the certificate.

Additional information The series includes the followings types:

Type	size (mm)
OABP202013 G/T	200X200X132
OABP203013 G/T	200X300X132
OABP204013 G/T	200X400X132
OABP303013 G/T	300X300X132
OABP304013 G/T	300X400X132
OABP306013 G/T	300X600X132
OABP404013 G/T	400X400X132
OABP406013 G/T	400X600X132

Extension frame height 55 mm

Other accessories:

Fastening lug	OFL1
Hinged cover screw	OLSH1
Hinged cover screw	OLSW1

For determining the electric strength, a test with voltage 5250 V according to IEC 60439-1 has been performed on the product. The product fulfills these requirements.

Based on: 256765-1, 277657-1, 297081-1 and 300793-3