



Dimensions and technical information p. 68-71

NOTE : please use Cat. No. when placing your order

Pack	Cat. Nos.	UC50 – support cradles								
1	<table border="0"> <tr> <td></td> <td>CM586040</td> <td></td> <td>CM586043</td> </tr> <tr> <td></td> <td>CM586048</td> <td></td> <td>CM586044</td> </tr> </table>		CM586040		CM586043		CM586048		CM586044	<p>↕ 30 → 54 mm ↔ 50 mm</p> <p>For technical information, see p. 68</p> <p> 12</p>
	CM586040		CM586043							
	CM586048		CM586044							

Pack	Cat. Nos.	CM50 – universal mounting plates (small)								
1	<table border="0"> <tr> <td></td> <td>CM586060</td> <td></td> <td>CM586063</td> </tr> <tr> <td></td> <td>CM586068</td> <td></td> <td>CM586064</td> </tr> </table>		CM586060		CM586063		CM586068		CM586064	<p>↕ 54 mm ↔ 50 mm</p> <p>For technical information, see p. 71</p>
	CM586060		CM586063							
	CM586068		CM586064							

Pack	Cat. Nos.	CAT30 – cantilever arm fixing plates								
1	<table border="0"> <tr> <td></td> <td>CM586050</td> <td></td> <td>CM586057</td> </tr> <tr> <td></td> <td>CM586058</td> <td></td> <td>CM586054</td> </tr> </table>		CM586050		CM586057		CM586058		CM586054	<p>↕ 30 → 54 mm ↔ 50 mm</p> <p>For technical information, see p. 69</p> <p> 20</p>
	CM586050		CM586057							
	CM586058		CM586054							

Pack	Cat. Nos.	CM50XL – universal mounting plates (large)								
1	<table border="0"> <tr> <td></td> <td>CM586130</td> <td></td> <td>CM586133</td> </tr> <tr> <td></td> <td>CM586138</td> <td></td> <td>CM586134</td> </tr> </table>		CM586130		CM586133		CM586138		CM586134	<p>↕ 54 ↔ 50 → 100 mm (side wire mounting)</p> <p>↕ 30 → 105 mm ↔ 100 → 600 mm (base wire mounting)</p> <p>For technical information, see p. 71</p>
	CM586130		CM586133							
	CM586138		CM586134							
1	<table border="0"> <tr> <td></td> <td>CM350880</td> <td colspan="2">EZ+ colour : black</td> </tr> </table>		CM350880	EZ+ colour : black						
	CM350880	EZ+ colour : black								

Pack	Cat. Nos.	CAT40 – channel fixing plates								
1	<table border="0"> <tr> <td></td> <td>CM586190</td> <td></td> <td>CM586197</td> </tr> <tr> <td></td> <td>CM586194</td> <td></td> <td>CM586194</td> </tr> </table>		CM586190		CM586197		CM586194		CM586194	<p>↕ 30 → 54 mm ↔ 50 mm</p> <p>For technical information, see p. 70</p> <p> 20</p>
	CM586190		CM586197							
	CM586194		CM586194							

	Pre-galvanised		Zinc rich coating
	Additional coating after electrogalvanisation (black)		Stainless steel 304 L
	Hot dip galvanised after manufacture		Stainless steel 316 L

For detailed information related to finishes, refer to **p. 132-133**

All dimensions (mm) are nominal