



Dimensions and technical information p. 92-95

NOTE : please use Cat. No. when placing your order

Pack	Cat. Nos.	UC50 – support cradles								
		\updownarrow 30 → 54 mm \leftrightarrow 50 mm For technical information, see p. 92 								
1	<table border="0"> <tr> <td></td> <td></td> </tr> <tr> <td>CM586040</td> <td>CM586043</td> </tr> <tr> <td></td> <td></td> </tr> <tr> <td>CM586048</td> <td>CM586044</td> </tr> </table>			CM586040	CM586043			CM586048	CM586044	12
CM586040	CM586043									
CM586048	CM586044									

Pack	Cat. Nos.	CAT30 – cantilever arm fixing plates								
		\updownarrow 30 → 54 mm \leftrightarrow 50 mm For technical information, see p. 93 								
1	<table border="0"> <tr> <td></td> <td></td> </tr> <tr> <td>CM586050</td> <td>CM586057</td> </tr> <tr> <td></td> <td></td> </tr> <tr> <td>CM586058</td> <td>CM586054</td> </tr> </table>			CM586050	CM586057			CM586058	CM586054	20
CM586050	CM586057									
CM586058	CM586054									

Pack	Cat. Nos.	CAT40 – universal mounting plates								
		\updownarrow 30 → 54 mm \leftrightarrow 50 mm For technical information, see p. 94 								
1	<table border="0"> <tr> <td></td> <td></td> </tr> <tr> <td>CM586190</td> <td>CM586197</td> </tr> <tr> <td></td> <td></td> </tr> <tr> <td>–</td> <td>CM586194</td> </tr> </table>			CM586190	CM586197			–	CM586194	20
CM586190	CM586197									
–	CM586194									

Pack	Cat. Nos.	CM50 – universal mounting plates (small)								
		\updownarrow 54 mm \leftrightarrow 50 mm For technical information, see p. 95 								
1	<table border="0"> <tr> <td></td> <td></td> </tr> <tr> <td>CM586060</td> <td>CM586063</td> </tr> <tr> <td></td> <td></td> </tr> <tr> <td>CM586068</td> <td>CM586064</td> </tr> </table>			CM586060	CM586063			CM586068	CM586064	12
CM586060	CM586063									
CM586068	CM586064									

Pack	Cat. Nos.	CM50XL – universal mounting plates (large)										
		\updownarrow 54 \leftrightarrow 50 → 100 mm (side wire mounting) \updownarrow 30 → 105 mm \leftrightarrow 100 → 600 mm (base wire mounting) For technical information, see p. 95 										
1	<table border="0"> <tr> <td></td> <td></td> </tr> <tr> <td>CM586130</td> <td>CM586133</td> </tr> <tr> <td></td> <td></td> </tr> <tr> <td>CM586138</td> <td>CM586134</td> </tr> <tr> <td></td> <td>CM350880</td> </tr> </table>			CM586130	CM586133			CM586138	CM586134		CM350880	9
CM586130	CM586133											
CM586138	CM586134											
	CM350880											

Key: Pre-galvanised	High Resistance*
Additional coating after electrogalvanisation (black)	Stainless steel 304 L
Hot dip galvanised after manufacture	Stainless steel 316 L

* For more information on High Resistance finish p. 12-13, 150
 For detailed information related to finishes, refer to p. 150-151

All dimensions (mm) are nominal