



Dimensions and technical information p. 141

NOTE : please use Cat. No. when placing your order

Pack	Cat. Nos.	Earth conductor clamps	
		BLF – earth conductor clamp (copper)	
		↕ 54 → 150 mm ↔ 50 → 600 mm	
		For technical information see p. 141	
	CU	L	Ø
		mm	mm ²
10	CM585387	BLF 6/16	1916
10	CM585397	BLF 6/35	2235
10	CM585407	BLF 6/50	2550



Pack	Cat. Nos.	Earth conductor clamps (continued)	
		GRIFEQUIP – earth conductor clamp (aluminium)	
		↕ 30 → 150 mm ↔ 50 → 600 mm	
		Not suitable for use with stainless steel	
		For technical information see p. 141	
	AL		
1	CM585327		
		GRIFEQUIP 2 – vertical clamp (aluminium)	
		↕ 30 → 150 mm ↔ 50 → 600 mm	
		Not suitable for use with stainless steel	
		For technical information see p. 141	
	AL		
1	CM585427		



		SCMT – cable support hook	
		↕ 30 → 150 mm ↔ 50 → 600 mm	
		For technical information, see p. 141	
	N		
	GS		
100	CM585080		



Key: GS Pre-galvanised	AL Aluminium
	CU Copper
For detailed information related to finishes, refer to p. 150-151	

All dimensions (mm) are nominal