












## Choix des supports jeux de barres

pour armoires Altis de distribution

		In maxi (A)	Barres cuivre plates			
			800	1000	1600	2500
<b>ALTIS AVEC CADRE SUPPORT PLASTRONS</b> 	<b>Montage pour 1 armoire</b> 	Supports	 0 373 90	 0 373 91	 0 373 92	 0 373 93
		Horizontal haut	P : 600			● + 0 473 16 + 0 480 26
		P : 800			● + 0 473 16	● + 0 473 16 + 0 480 27
		P : 1000			● + 0 473 16	● + 0 473 16
	Transfert horizontal ou horizontal bas 	P : 600			● + (2x) 0 480 26 + 0 473 16 + 0 480 27 <sup>(1)</sup>	
		P : 800			● + (2x) 0 480 27 + 0 473 16 <sup>(1)</sup>	● + (3x) 0 480 27 + 0 473 16 <sup>(1)</sup>
		P : 1000				● + 0 480 28 + 0 480 27 + 0 473 16 <sup>(3)</sup>
	Vertical latéral dans gaine 	P : 400	●	●	●	
		P : 500	● + 0 480 33 <sup>(2)</sup>	● + 0 480 33 <sup>(2)</sup>	● + 0 480 33 <sup>(2)</sup>	
		P : 600	● + 0 480 33	● + 0 480 33	● + 0 480 33	●
		P : 800/1000	● + 0 480 33	● + 0 480 33	● + 0 480 33	● + 0 480 33
	Vertical latéral dans l'armoire 	P : 800	● + 0 480 33	● + 0 480 33	● + 0 480 33	
		P : 400				
	Vertical fond d'armoire 	P : 500	● + 0 480 33		● + 0 480 33	
P : 600		● + 0 480 33		● + 0 480 33	●	
P : 800		● + 0 480 33		● + 0 480 33	●	
Horizontal fond d'armoire 	P : 400					
	P : 500	● + 0 480 27		● + 0 480 27		
	P : 600	● + 0 480 27		● + 0 480 27	● + 0 480 27	
	P : 800	● + 0 480 27		● + 0 480 27	● + 0 480 27	










1 : Montage avec montant réf. 0 474 80 uniquement

2 : Utiliser les kits d'assemblage d'armoires réf. 0 476 81 ou 0 476 82 uniquement

3 : Armoire profondeur 1000 sur demande

## Choix des supports jeux de barres

répartition standard Altis

		In maxi (A)	Barres cuivre plates			
			800	1000	1600	4000
<b>ALTIS SANS CADRE SUPPORT PLASTRONS</b> 	<b>Montage</b> 	Supports	 0 373 90	 0 373 91	 0 373 92	 0 373 93
		Principal horizontal haut ou bas 	P : 400			●
	P : 600				● + 0 473 15	●
	P : 800				● + 0 473 16	●
	P : 1000				● + 0 473 17	● + 0 473 17
	Vertical latéral 	P : 400	●	●	●	
		P : 600	● + 0 473 15	● + 0 473 15	● + 0 473 15	●
		P : 800	● + 0 473 16	● + 0 473 16	● + 0 473 16	●
		P : 1000	● + 0 473 17	● + 0 473 17	● + 0 473 17	● + 0 473 17
	Vertical en fond 	L : 400	●		●	
		L : 600	● + 0 473 15		● + 0 473 15	
		L : 800	● + 0 473 16		● + 0 473 16	
		L : 1000	● + 0 473 17		● + 0 473 17	