
















Céliane™

plaques spéciales et supports universels (suite)

Mécanismes Céliane :	0 673 55 0 670 86 0 671 59 5 x 0 670 01/31 0 671 33/34	Prise 2P+T quadruple précâblée compacte 0 671 28	
▼	 Plaque 4/5 modules	 Plaque 6/8 modules	
MATIÈRES*			
Inox Brossé		0 691 05 + 0 802 52	0 691 06 + 0 802 53
Nickel Velours		0 691 15 + 0 802 52	-
Black Nickel		0 690 35 + 0 802 52	0 690 36 + 0 802 53
Bronze Doré		0 691 35 + 0 802 52	-
Chêne Blanchi		0 690 55 + 0 802 52	-
Teinté Wengué ⁽²⁾		0 692 05 + 0 802 52	-
Erable		0 692 15 + 0 802 52	-
Corian® Cannelé ⁽¹⁾		0 690 15 + 0 802 52	-
Corian® Gougé ⁽¹⁾		0 690 25 + 0 802 52	-
Ardoise		0 693 75 + 0 802 52	-
Verre Kaolin		0 693 15 + 0 802 52	-
Verre Piano		0 693 05 + 0 802 52	-
Verre Miroir		0 691 25 + 0 802 52	-

1 : Marque déposée de DuPont de Nemours

2 : Frêne teinté wengué

* Les plaques finitions Bois et Ardoise sont des pièces uniques en matière naturelle dont l'aspect et la teinte peuvent varier d'un exemplaire à l'autre