









# dooxie™ composable

## tableau de choix plaques




























### VERSION BLANCHE

 <b>6 008 01</b> <b>6 009 41</b> (livré par 100)	 <b>6 009 80</b>	 <b>6 008 02</b>	 <b>6 008 03</b>	 <b>6 008 04</b>
--	--	--	---	--

### PLAQUES SPÉCIALES

 <b>6 009 42</b> Avec porte-étiquette	 <b>6 009 43</b> IP 44	 <b>6 009 44</b> A volet IP 44 - IK 07	 <b>6 008 07</b> Compatible avec transformeur réf. 6 003 28 et prise faible profondeur easyréno réf. 6 000 31
--	---	---	--

### VERSION COULEUR

	1 poste	2 postes	3 postes	4 postes	1 poste
Dune	 <b>6 008 11</b>	 <b>6 008 12</b>	 <b>6 008 13</b>	 <b>6 008 14</b>	 <b>6 009 70</b>
Plume	 <b>6 008 21</b>	 <b>6 008 22</b>	 <b>6 008 23</b>	 <b>6 008 24</b>	 <b>6 009 71</b>
Blanc bague effet chromé	 <b>6 008 41</b>	 <b>6 008 42</b>	 <b>6 008 43</b>	-	 <b>6 009 73</b>
Effet Aluminium	 <b>6 008 51</b>	 <b>6 008 52</b>	 <b>6 008 53</b>	 <b>6 008 54</b>	 <b>6 009 75</b>
Effet inox brossé	 <b>6 008 71</b>	 <b>6 008 72</b>	 <b>6 008 73</b>	-	 <b>6 009 78</b>
Effet bois ébène	 <b>6 008 81</b>	 <b>6 008 82</b>	 <b>6 008 83</b>	-	 <b>6 009 79</b>