

Luminaires à lampes E27

tableau de choix

Conso (W)	Gamme	ON/OFF		Détection HF	
		Standard	Antivandale	Standard	Antivandale
53 W / 17 W	Chartres Origine ovales/ovales grille, verticale (p. 793) 	544270 544276	-	-	-
53 W / 20 W maxi	Chartres Origine (p. 792) 	Ø 296 mm 514270 514276 514283	Ø 309 mm 714270	Ø 296 mm 514570 514576 514573	Ø 309 mm 714570
	Super 400 (p. 794) 	-	-	Ø 296 mm diffuseur polycarbonate 500570 500576	Ø 296 mm diffuseur polycarbonate 700570 700576
70 W / 20 W maxi	MAP 400 (p. 795) 	Ø 230 mm 400270	-	-	-
	Prestichoc (p. 795) 	Ø 230 mm 413270	-	-	-
70 W / 23 W maxi	Super 400 (p. 794) 	Ø 296 mm diffuseur polycarbonate 500270 500276	Ø 296 mm diffuseur polycarbonate 700270 700276	-	-
	Chartres Origine (p. 792) 	Ø 340 mm 524270	Ø 350 mm 724270	Ø 340 mm 524570	Ø 350 mm 724570