




































































		SOLUTIONS MURALES			
		 BOITES D'ENCASTREMENT (p. 929)	 CADRES SAILLIE (p. 927)	 SUPPORTS (p. 926)	 PLAQUES (p. 924)
	2 modules	 0 771 11L ou  0 771 45L (prof 50 mm)		 0 802 51	 0 788 02L
	2 x 2 modules	 0 771 34		 0 802 52	 0 788 04L
	2 x 2 modules	 2 x 0 771 11L ou  2 x 0 771 45L (prof 50 mm)		 0 802 52	 0 788 22L
	3 x 2 modules	 0 771 36		 0 802 53	 0 788 06L
	3 x 2 modules	 3 x 0 771 11L ou  3 x 0 771 45L (prof 50 mm)		 0 802 53	 0 788 23L
	4 x 2 modules	 2 x 0 771 34		 0 802 54	 0 788 08L
	2 x 2 x 2 modules	 2 x 0 771 34		 0 802 64	 0 788 38L
	2 x 3 x 2 modules	 2 x 0 771 36		 0 802 66	 0 788 32L
TOUTES LES CONFIGURATIONS SONT POSSIBLES AVEC L'ACCESSOIRE DE RACCORDEMENT MOSAIC LINK 0 771 00L (p. 923)					
	4 modules	 0 771 42L		 0 802 52	 0 788 14L
	6 modules	 0 771 42L +  0 771 00L +  0 771 45L		 0 802 53	 0 788 16L
	8 modules	 0 771 42L +  0 771 00L +  0 771 42L		 0 802 53	 0 788 18L
	2 x 6 modules	 2 x 0 771 42L +  2 x 0 771 00L +  2 x 0 771 45L		 0 802 66	 0 788 36L
	2 x 8 modules	 2 x 0 771 42L +  2 x 0 771 00L +  2 x 0 771 42L		 0 802 66	 0 788 37L