MCBs TX³ 10000

thermal magnetic MCBs from 2 A to 63 A - B and C curves

4 041 71

4 042 09

4 042 28



Technical characteristics, **please consult the technical datasheet**

Conform to IEC 60898-1
Compatible with prong-type and fork type supply busbars
Equipped with special DIN rail clamp allowing independent MCB removal with supply busbar in place
Breaking capacity:
10000 - IEC 60898-1 - 230/400 V~
10 kA - IEC 60947-2 - 230/400 V~
Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls (p. 73-74)
Do not accept add-on modules

Single pole 230/400 V~

Pack	Cat.Nos		Nominal rating In (A)	Number of modules
	B curve	C curve		
10	4 040 78	4 041 64	2	1
10	4 040 81	4 041 67	6	1
10	4 040 82	4 041 69	10	1
10	4 040 83	4 041 70	13	1
10	4 040 84	4 041 71	16	1
10	4 040 85	4 041 72	20	1
10	4 040 86	4 041 73	25	1
10	4 040 87	4 041 74	32	1
10	4 040 88	4 041 75	40	1
10	4 040 89	4 041 76	50	1
10	4 040 90	4 041 77	63	1

2-pole 230/400 V~

			Nominal rating In (A)	Number of modules
	B curve	C curve		
5	4 041 06	4 041 98	2	2
5	4 041 09	4 042 01	6	2
5	4 041 10	4 042 03	10	2
5	4 041 11	4 042 04	13	2
5	4 041 12	4 042 05	16	2
5	4 041 13	4 042 06	20	2
5	4 041 14	4 042 07	25	2
5	4 041 15	4 042 08	32	2
5	4 041 16	4 042 09	40	2
5	4 041 17	4 042 10	50	2
5	4 041 18	4 042 11	63	2

3-pole 400 V~

Pack	Cat.Nos		Nominal rating In (A)	Number of modules
	B curve	C curve		
1	4 041 20	4 042 15	2	3
1	4 041 23	4 042 18	6	3
1	4 041 24	4 042 20	10	3
1	4 041 25	4 042 21	13	3
1	4 041 26	4 042 22	16	3
1	4 041 27	4 042 23	20	3
1	4 041 28	4 042 24	25	3
1	4 041 29	4 042 25	32	3
1	4 041 30	4 042 26	40	3
1	4 041 31	4 042 27	50	3
1	4 041 32	4 042 28	63	3

4-pole 400 V~

			Nominal rating In (A)	Number of modules
	B curve	C curve		
1	4 041 48	4 042 49	6	4
1	4 041 51	4 042 52	6	4
1	4 041 52	4 042 54	10	4
1	4 041 53	4 042 55	13	4
1	4 041 54	4 042 56	16	4
1	4 041 55	4 042 57	20	4
1	4 041 56	4 042 58	25	4
1	4 041 57	4 042 59	32	4
1	4 041 58	4 042 60	40	4
1	4 041 59	4 042 61	50	4
1	4 041 60	4 042 62	63	4

See the video