

MCBs DX³ 10000 - 16 kA

thermal magnetic MCBs from 2 A to 125 A - D curve



Performance of DX³ MCBs and auxiliaries **p. 76-77**

Conform to IEC 60898-1

Compatible with both prong-type and fork type supply busbars (except 80 A, 100 A and 125 A MCBs)

Breaking capacity:

10000 - IEC 60898-1 - 400 V~

16 kA - IEC 60947-2 - 400 V~

Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls (p. 73-74) and add-on modules (p. 71-72)

Pack Cat.Nos Single pole 230/400 V~

Pack	Cat.Nos	Nominal rating In (A)	Number of modules
1	4 094 25	2	1
1	4 094 28	6	1
1	4 094 30	10	1
1	4 094 32	16	1
1	4 094 33	20	1
1	4 094 34	25	1
1	4 094 35	32	1
1	4 094 36	40	1
1	4 094 37	50	1
1	4 094 38	63	1

Pack Cat.Nos 2-pole 230/400 V~

Pack	Cat.Nos	Nominal rating In (A)	Number of modules
1	4 094 44	2	2
1	4 094 47	6	2
1	4 094 49	10	2
1	4 094 51	16	2
1	4 094 52	20	2
1	4 094 53	25	2
1	4 094 54	32	2
1	4 094 55	40	2
1	4 094 56	50	2
1	4 094 57	63	2
1	4 094 58	80	3
1	4 094 59	100	3
1	4 094 60	125	3

Pack Cat.Nos 3-pole 400 V~

Pack	Cat.Nos	Nominal rating In (A)	Number of modules
1	4 094 92	2	3
1	4 094 95	6	3
1	4 094 97	10	3
1	4 094 99	16	3
1	4 095 00	20	3
1	4 095 01	25	3
1	4 095 02	32	3
1	4 095 03	40	3
1	4 095 04	50	3
1	4 095 05	63	3
1	4 095 06	80	4.5
1	4 095 07	100	4.5
1	4 095 08	125	4.5

Pack Cat.Nos 4-pole 400 V~

Pack	Cat.Nos	Nominal rating In (A)	Number of modules
1	4 095 26	2	4
1	4 095 29	6	4
1	4 095 31	10	4
1	4 095 33	16	4
1	4 095 34	20	4
1	4 095 35	25	4
1	4 095 36	32	4
1	4 095 37	40	4
1	4 095 38	50	4
1	4 095 39	63	4
1	4 095 40	80	6
1	4 095 41	100	6
1	4 095 42	125	6