

LEGRAND PACKAGING

Practical & eco-friendly

Legrand packaging – your assistance of a certified original product which is factory inspected, protected and clearly identifiable



Dustproof flaps: effective protection of the product

Resealable box: for easy management of the contents

Informative label:
 - Catalogue number/quantity
 - Picture of the product
 - Clear description
 - Technical information
 - Barcode
 - Regulatory marking

The red and white box and the logo are registered trademarks

Eco-friendly:
 - Recyclable cardboard packaging
 - Printing inks comply with environmental standards



www.legrand-copytracer.com

Copytracer involves a unique registration number that appears on some of our products. This number is stored in a database and can be consulted on this website. By entering it you can immediately check whether or not the Copytracer number is consistent with your product.



Isolating fuse carriers



0 058 06



0 058 28



0 058 48

Pack	Cat.Nos	For industrial cylindrical cartridge fuses type aM or G		
		Conform to standard IEC 60269-2 Isolators conform to IEC 60947-3 Icc: - 20 kA with 8.5 x 31.5 cartridge fuse - 100 kA with 10 x 38 cartridge fuse Fuse not supplied (p. 261)		
		Single pole		
		Cartridge dimensions (mm)	Voltage	Number of modules
10	0 058 06 ¹	8.5 x 32	400 V~	1
10	0 058 08	10 x 38	500 V~	1
		Single pole + neutral		
10	0 058 16 ¹	8.5 x 32	400 V~	1
10	0 058 18	10 x 38	500 V~	1
		2-pole		
5	0 058 26 ¹	8.5 x 32	400 V~	2
5	0 058 28	10 x 38	500 V~	2
		3-pole		
3	0 058 36 ¹	8.5 x 32	400 V~	3
3	0 058 38	10 x 38	500 V~	3
		3-pole + neutral		
2	0 058 46 ¹	8.5 x 32	400 V~	4
2	0 058 48	10 x 38	500 V~	4
		Accessoires		
10	0 057 90	Blow-out indicator 250 V~		
				
1	0 057 96	Early break N/O + N/C contact auxiliary 5 A - 250 V~ (0.5 module)		
2	4 063 04	Sealable screw cover (4 separable poles)		
				

1: Previously 8.5 x 31.5 mm