

CX³ changeover switches, push-buttons and control switches



Technical characteristics p. 99

Pack	Cat.Nos	Changeover switches		Pack	Cat.Nos	Maintained contact control switches	
		Conform to IEC 60669-1 Nominal rating 32 A Compatible with fluorescent lamps (20 AX) Two-way - 250 V~				Conform to IEC 60669-1 Nominal rating 20 A - 250 V~ Compatible with fluorescent lamps (20 AX) Maximum power with self-ballasted lamps (SBL): 250 W Accept prong-type supply busbars Single function control switches	
10	4 129 00		Number of modules 1	10	4 129 10	2 NO	1
5	4 129 01	Double two-way - 400 V~ 	2	10	4 129 11	1 NO + NC	1
10	4 129 02	Two way with centre point - 250 V~ 	1	10	4 129 12	Dual functions control switches with indicator 1 NO + green LED indicator 12/48 V~/=	1
5	4 129 03	Double two way with centre point - 250 V~ 	2	10	4 129 13	1 NC + red LED indicator 12/48 V~/=	1
10	4 129 04	Switch NO + NC - 250 V~ 	1	10	4 129 14	1 NO + green LED indicator 110/400 V~	1
		Momentary contact push-buttons Conform to IEC 60669-1 Nominal rating 20 A - 250 V~ Compatible with fluorescent lamps (20 AX) Accept prong-type supply busbars Single function push-buttons				1 NC + red LED indicator 110/400 V~	1
10	4 129 08	1 NO	1	10	4 129 16	Dual functions push-buttons without indicator 1 NO (green push-button) + 1 NC (red push-button)	1
10	4 129 09	1 NC	1	10	4 129 18	Dual functions push-buttons with indicator 1 NO + green LED indicator 12/48 V~/=	1
10	4 129 16			10	4 129 19	1 NC + red LED indicator 12/48 V~/=	1
10	4 129 18			10	4 129 20	1 NO + green LED indicator 100/400 V~	1
10	4 129 19			10	4 129 40	1 NC + red LED indicator 100/400 V~	1