

# DRX™ 630 accessories



Pack	Cat.Nos	Rotary handles
1	0 272 50	<b>Direct</b> Standard (grey)
1	0 272 51	<b>Vari-depth handle</b> Comprising: connecting rod, bracket, drilling template, mounting accessories, door locking mechanism Standard (grey)
<b>Connection accessories</b>		
1	0 262 30	<b>Insulating shields</b> Used to isolate the connection between each pole Set of 2 pieces
1	0 262 44   0 262 45	<b>Sealable terminal shields</b> Set of 2
1	4 222 34   4 222 35	<b>IP 20 terminal cover</b> Set of two terminal covers
1	0 262 50	<b>Cage terminals</b> Set of 4 cage terminals for cables
1	0 262 51	Set of 4 high capacity cage terminals for cables
1	0 262 47	<b>Extended front terminals</b> Set of 4 extended front terminals
1	0 262 48   0 262 49	<b>Spreaders</b> Set of incoming or outgoing spreaders
1	0 263 50   0 263 51	<b>Swivel terminals</b> Set of incoming or outgoing swivel terminals
1	0 263 52   0 263 53	<b>Flat terminals</b> Set of incoming or outgoing flat terminals



Pack	Cat.Nos	Padlock for DRX 630
1	0 262 40	For locking on "OFF" position (up to 3 locks)
<b>Control and signalling auxiliaries for DRX 630</b>		
For DPX <sup>3</sup> , DPX <sup>3</sup> -I and DRX		
1	4 210 11	<b>Auxiliary contact or fault signal</b> For signalling the state of the contacts or opening of the MCCB on a fault Changeover switch 3 A - 240 V~
<b>Shunt releases</b>		
Shunt inrush power 300 V~		
Coil voltage		
1	4 222 39	24 V~ and =
1	4 222 40	48 V~ and =
1	4 222 41	110 V~ and =
1	4 222 42	230 V~ and =
1	4 222 43	400 V~ and =
<b>Undervoltage releases</b>		
Undervoltage power consumption 5 V~		
Coil voltage		
1	4 222 44	24 =
1	4 222 45	24 V~
1	4 222 46	48 V=
1	4 222 47	110-125 V~
1	4 222 48	220-240 V~
1	4 222 49	380-415 V~