

DRX™ 250 HP

thermal magnetic MCCBs from 16 to 250 A



DRX™ 250 HP adjustable

thermal magnetic MCCBs from 16 to 250 A



6 674 19



6 674 34



6 690 90



6 691 10

Dimensions and installation principle **p. 154**
 Technical characteristics and curves **p. 156-157**

For switching, control, isolation and protection of low-voltage electrical lines. Can be fitted with auxiliaries (p. 149). Supplied with: screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P). Fixed thermal and magnetic
 Conform to IEC 60947-2

Dimensions and installation principle **p. 154**
 Technical characteristics and curves **p. 156-157**

For switching, control, isolation and protection of low-voltage electrical lines. Can be fitted with auxiliaries (p. 149). Supplied with: screw terminals, fixing screws, insulating shields (2 for 3P and 3 for 4P). Adjustable thermal and magnetic
 Conform to IEC 60947-2

Pack	Cat.Nos		DRX 250 HP
	3P	4P	
			Breaking capacity Icu 25 kA (415 V~)
			In
1	6 694 10	6 694 25	16 A
1	6 694 11	6 694 26	20 A
1	6 694 12	6 694 27	25 A
1	6 694 13	6 694 28	32 A
1	6 694 14	6 694 29	40 A
1	6 694 15	6 694 30	50 A
1	6 694 16	6 694 31	63 A
1	6 694 17	6 694 32	80 A
1	6 694 18	6 694 33	100 A
1	6 694 19	6 694 34	125 A
1	6 694 20	6 694 35	160 A
1	6 694 21	6 694 36	180 A
1	6 694 22	6 694 37	200 A
1	6 694 23	6 694 38	225 A
1	6 694 24	6 694 39	250 A
			Breaking capacity Icu 36 kA (415 V~)
1	6 694 40	6 694 55	16 A
1	6 694 41	6 694 56	20 A
1	6 694 42	6 694 57	25 A
1	6 694 43	6 694 58	32 A
1	6 694 44	6 694 59	40 A
1	6 694 45	6 694 60	50 A
1	6 694 46	6 694 61	63 A
1	6 694 47	6 694 62	80 A
1	6 694 48	6 694 63	100 A
1	6 694 49	6 694 64	125 A
1	6 694 50	6 694 65	160 A
1	6 694 51	6 694 66	180 A
1	6 694 52	6 694 67	200 A
1	6 694 53	6 694 68	225 A
1	6 694 54	6 694 69	250 A
			Breaking capacity Icu 50 kA (415 V~)
1	6 674 10	6 674 25	16 A
1	6 674 11	6 674 26	20 A
1	6 674 12	6 674 27	25 A
1	6 674 13	6 674 28	32 A
1	6 674 14	6 674 29	40 A
1	6 674 15	6 674 30	50 A
1	6 674 16	6 674 31	63 A
1	6 674 17	6 674 32	80 A
1	6 674 18	6 674 33	100 A
1	6 674 19	6 674 34	125 A
1	6 674 20	6 674 35	160 A
1	6 674 21	6 674 36	180 A
1	6 674 22	6 674 37	200 A
1	6 674 23	6 674 38	225 A
1	6 674 24	6 674 39	250 A

Pack	Cat.Nos		DRX 250 HP
	3P	4P	
			Thermal adjustable from 0.8 to 1 x In Magnetic adjustable from 5 to 10 x In
			Breaking capacity Icu 25 kA (415 V~)
			In
1	6 690 00	6 690 20	16 A
1	6 690 01	6 690 21	20 A
1	6 690 02	6 690 22	25 A
1	6 690 03	6 690 23	32 A
1	6 690 04	6 690 24	40 A
1	6 690 05	6 690 25	50 A
1	6 690 06	6 690 26	63 A
1	6 690 07	6 690 27	80 A
1	6 690 08	6 690 28	100 A
1	6 690 09	6 690 29	125 A
1	6 690 10	6 690 30	160 A
1	6 690 11	6 690 31	200 A
1	6 690 12	6 690 32	250 A
			Breaking capacity Icu 36 kA (415 V~)
1	6 690 40	6 690 60	16 A
1	6 690 41	6 690 61	20 A
1	6 690 42	6 690 62	25 A
1	6 690 43	6 690 63	32 A
1	6 690 44	6 690 64	40 A
1	6 690 45	6 690 65	50 A
1	6 690 46	6 690 66	63 A
1	6 690 47	6 690 67	80 A
1	6 690 48	6 690 68	100 A
1	6 690 49	6 690 69	125 A
1	6 690 50	6 690 70	160 A
1	6 690 51	6 690 71	200 A
1	6 690 52	6 690 72	250 A
			Breaking capacity Icu 50 kA (415 V~)
1	6 690 80	6 691 00	16 A
1	6 690 81	6 691 01	20 A
1	6 690 82	6 691 02	25 A
1	6 690 83	6 691 03	32 A
1	6 690 84	6 691 04	40 A
1	6 690 85	6 691 05	50 A
1	6 690 86	6 691 06	63 A
1	6 690 87	6 691 07	80 A
1	6 690 88	6 691 08	100 A
1	6 690 89	6 691 09	125 A
1	6 690 90	6 691 10	160 A
1	6 690 91	6 691 11	200 A
1	6 690 92	6 691 12	250 A