

## DPX<sup>3</sup> 160 HP - thermal magnetic release

MCCBs up to 160 A - fixing on plate



4 237 25



4 237 26

Dimensions **p. 190**  
 Electrical characteristics **p. 193**

Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines

Can be fitted with auxiliaries (p. 175)

Supplied with: screws for connections, fixing screws and insulated shields (phase barriers)

Can be fitted with cage terminals 120 mm<sup>2</sup> max. (flexible cable) or 150 mm<sup>2</sup> max. rigid cable (p. 169)

Conform to IEC 60947-2 - Sealable adjustment

Can be mounted on plate in XL<sup>3</sup> and XL<sup>3</sup> S cabinets and enclosures

Pack	Cat.Nos	MCCBs thermal magnetic release - fixed version
1	3P   4P 4 237 20   4 237 21	Thermal adjustable from 0.8 to 1 In Magnetic fixed at 10 In <b>Breaking capacity Icu 36 kA (400 V<sub>~</sub>)</b> In (A) 160
1	4 237 25   4 231 26	<b>Breaking capacity Icu 50 kA (400 V<sub>~</sub>)</b> 160
1	4 237 30   4 237 31	<b>Breaking capacity Icu 70 kA (400 V<sub>~</sub>)</b> 160
1	4 237 35   4 237 36	<b>Breaking capacity Icu 100 kA (400 V<sub>~</sub>)</b> 160
<b>MCCBs thermal magnetic release with electronic earth leakage module - fixed version</b>		
1	4P 4 237 23	Thermal adjustable from 0.8 to 1 In Magnetic fixed at 10 In Equipped with earth leakage module Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A Adjustable tripping: 0 - 0.3 - 1 - 3 s (with 0.03 A possible only 0 s) <b>Breaking capacity Icu 36 kA (400 V<sub>~</sub>)</b> In (A) 160
1	4 237 28	<b>Breaking capacity Icu 50 kA (400 V<sub>~</sub>)</b> 160

DPX<sup>3</sup>-I 160 HP trip-free switches  
**p. 186**

## DPX<sup>3</sup> 125 HP and 160 HP

equipment and accessories



4 238 84



4 238 76



4 238 35

Pack	Cat.Nos	Rotary handles
1	4 238 70	<b>Direct on DPX<sup>3</sup></b> Standard (grey)
1	4 238 71	For emergency use (red/yellow)
<b>Vari-depth handle IP 55</b>		
Comprising: connection rod, bracket, self-adhesive drilling template, mounting accessories and door lock mechanism		
1	4 238 72	Standard (grey)
1	4 238 73	For emergency use (red/yellow)
<b>Locking accessories for vari-depth handles</b>		
To be equipped with universal keylocks Cat.Nos 4 238 80/81/82/83 (p. 175)		
1	4 238 05	For vari-depth handle Cat.Nos 4 238 02/03 (p. 174) and 4 238 72/73
<b>Connection accessories</b>		
<b>Insulated shields (phase barriers)</b>		
1	4 238 34	Set of 2 insulated shields for DPX <sup>3</sup> 125/160/250 HP 3P
1	4 238 35	Set of 3 insulated shields for DPX <sup>3</sup> 125/160/250 HP 4P
<b>Padlock</b>		
1	4 210 49	Padlock for locking in "open" position For DPX <sup>3</sup> 160/250 and DPX <sup>3</sup> 125/160/250 HP
<b>Cage terminals</b>		
For Cu/Al cables, 1 x 70 mm <sup>2</sup> for flexible and rigid cables (for Al cables In max 80 A)		
1	4 238 84	Set of 3 terminals for DPX <sup>3</sup> 125/160 HP 3P
1	4 238 85	Set of 4 terminals for DPX <sup>3</sup> 125/160 HP 4P
<b>High capacity cage terminals</b>		
For Cu/Al cables, 1 x 120 mm <sup>2</sup> for flexible cables and 1 x 150 mm <sup>2</sup> for rigid cable		
1	4 238 76	Set of 3 terminals for DPX <sup>3</sup> 125/160 HP 3P
1	4 238 77	Set of 4 terminals for DPX <sup>3</sup> 125/160 HP 4P
<b>Spreaders</b>		
For incoming bars or cable lugs		
1	4 238 88	Set of 3 spreaders for DPX <sup>3</sup> 125/160 HP 3P
1	4 238 89	Set of 4 spreaders for DPX <sup>3</sup> 125/160 HP 4P
<b>Rear terminals</b>		
Used to convert a fixed version with front terminals to a fixed version with rear terminals		
1	4 238 91	Set of 3 rear terminals for DPX <sup>3</sup> 125/160 HP 3P
1	4 238 92	Set of 4 rear terminals for DPX <sup>3</sup> 125/160 HP 4P
<b>Sealable terminal shields</b>		
<b>For front terminals</b>		
1	4 238 93	For DPX <sup>3</sup> 125/160 HP 3P
1	4 238 94	For DPX <sup>3</sup> 125/160 HP 4P
<b>Mechanical interlock for transfer switches</b>		
1	4 238 27	Interlocking mechanism for 2 fixed DPX <sup>3</sup> 125/160/250 HP MCCBs
1	4 238 28	Interlocking mechanism for 2 fixed DPX <sup>3</sup> 125/160/250 HP MCCBs with electronic module
1	4 238 25	Plate for mounting and interlocking of 2 DPX <sup>3</sup> 125/160 HP

Disengageable rotary handles  
**p. 165**

Universal key locks for DPX<sup>3</sup> 125/160/250 HP  
**p. 175**