

DPX³ 250 HP

S10 configurable electronic release MCCBs from 40 to 250 A - fixing on plate

January 2024



4 234 23



4 234 28



4 234 38

Dimensions **p. 191-192**
Electrical characteristics **p. 193**

Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines. Can be fitted with auxiliaries (p. 175)
Supplied with: screws for connection fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)
Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable (p. 175)
Can be mounted on plate in XL³ and XL³ S cabinets and enclosures
Conform to IEC 60947-2

Pack	Cat.Nos		MCCBs S10 configurable electronic release - fixed version
			Breaking capacity Icu 36 kA (400 V~)
	3P	4P	In (A)
1	4 234 00	4 234 05	40
1	4 234 01	4 234 06	100
1	4 234 02	4 234 07	160
1	4 234 03	4 234 08	250
			Breaking capacity Icu 50 kA (400 V~)
1	4 234 20	4 234 25	40
1	4 234 21	4 234 26	100
1	4 234 22	4 234 27	160
1	4 234 23	4 234 28	250
			Breaking capacity Icu 70 kA (400 V~)
1	4 234 40	4 234 45	40
1	4 234 41	4 234 46	100
1	4 234 42	4 234 47	160
1	4 234 43	4 234 48	250
			Breaking capacity Icu 100 kA (400 V~)
1	4 234 50	4 234 55	40
1	4 234 51	4 234 56	100
1	4 234 52	4 234 57	160
1	4 234 53	4 234 58	250

Pack	Cat.Nos	MCCBs S10 configurable electronic release with electronic earth leakage module - fixed version
		Breaking capacity Icu 36 kA (400 V~)
	4P	In (A)
1	4 234 15	40
1	4 234 16	100
1	4 234 17	160
1	4 234 18	250
		Breaking capacity Icu 50 kA (400 V~)
1	4 234 35	40
1	4 234 36	100
1	4 234 37	160
1	4 234 38	250

DPX³-I 250 HP trip-free switches
p. 186

DPX³ 250 HP magnetic release only
p. 187

Signalling and control accessories
p. 175

Red catalogue numbers: New products