



Pack	Cat.Nos	
		<b>Plug-in version</b>
		A DPX <sup>3</sup> HP plug-in version is a DPX <sup>3</sup> HP fitted with a plug-in mobile part kit and mounted on a plug-in base
1	4 238 50   4 238 51	<b>Plug-in bases</b> For DPX <sup>3</sup> 250 HP
1	4 238 52   4 238 53	<b>Plug-in mobile part kit</b> For DPX <sup>3</sup> 250 HP
1	4 238 63	<b>Locking support</b> Locking support for plug-in version. To be equipped with universal keylocks Cat.Nos 4 238 80/81/82/83 (p. 175)
		<b>Draw-out version</b>
		A DPX <sup>3</sup> HP draw-out version is a plug-in DPX <sup>3</sup> HP fitted with a "Debro-lift mechanism" and a "Draw-out front cover mask" which can be used to withdraw the DPX <sup>3</sup> HP while keeping it on its base
1	4 238 60   4 238 61	<b>Debro-lift mechanism</b> For DPX <sup>3</sup> 250 HP ; Supplied with handle
1	4 238 55	<b>Draw-out front cover masks</b> For DPX <sup>3</sup> 250 HP alone
1	4 238 56	For DPX <sup>3</sup> 250 HP with motor-driven handle
1	4 238 62	<b>Locking support in draw-out position</b> Enable locking of DPX <sup>3</sup> 250 HP in draw-out position. To be equipped with universal keylocks Cat.Nos 4 238 80/81/82/83 (p. 175)
1	4 238 64	<b>Padlock in draw-out position</b> Enable padlocking of DPX <sup>3</sup> HP in draw-out position
1	4 222 30	<b>Auxiliary contact</b> Automatic auxiliary contact for DPX <sup>3</sup> HP draw-out version (up to 2 contacts by DPX <sup>3</sup> HP)
1	0 098 19	<b>Set of connectors for plug-in and draw-out versions</b> Signalling contact plugged-in / drawn-out
1	4 210 48	<b>Signalling contact</b> For DPX <sup>3</sup> 160/250 and DPX <sup>3</sup> 250 HP plug-in versions

Pack	Cat.Nos	
		<b>Mechanical interlock for transfer switches</b>
1	4 238 27	Interlocking mechanism for 2 fixed DPX <sup>3</sup> 125/250 HP MCCBs
1	4 238 28	Interlocking mechanism for 2 fixed DPX <sup>3</sup> 125/250 HP MCCBs with electronic module
1	4 238 29	Rear interlocking mechanism for 2 plug-in / draw-out DPX <sup>3</sup> 250 HP MCCBs
1	4 238 26	Plate for mounting and interlocking of 2 DPX <sup>3</sup> 250 HP
		<b>Rotary handles</b>
		<b>Direct on DPX<sup>3</sup></b>
1	4 238 00	Standard (grey)
1	4 238 01	For emergency use (red/yellow)
		<b>Vari-depth handle IP 55</b>
		Comprising: connection rod, bracket, self-adhesive drilling template, mounting accessories and door lock mechanism
1	4 238 02	Standard (grey)
1	4 238 03	For emergency use (red/yellow)
		<b>Locking supports for rotary handles</b>
		To be equipped with universal keylocks Cat.Nos 4 238 80/81/82/83 (p. 175)
1	4 238 04	For direct handle Cat.Nos 4 238 00/01
1	4 238 05	For vari-depth handle Cat.Nos 4 238 02/03 and 4 238 72/73 (p. 169)
		<b>Auxiliary contact for rotary handles</b>
1	4 238 06	1 N/C + 1 N/O auxiliary contact for rotary handles
		<b>Disengageable rotary handles</b>
		<b>Direct on DPX</b>
1	4 238 14	Standard handle (black)
1	4 238 15	Handle for emergency use (red/yellow)
		<b>Vari-depth handle</b>
		Comprising: connection rod, bracket, self adhesive drilling template, mounting accessories and door locking mechanism
1	4 238 16	Standard handle (black)
1	4 238 17	Handle for emergency use (red/yellow)
		<b>Motor-driven handles</b>
		<b>Front installation motor operators</b>
1	4 238 40	24 V $\sim$ /=
1	4 238 41	48 V $\sim$ /=
1	4 238 42	110 V $\sim$
1	4 238 43	230 V $\sim$
		<b>Locking accessories for motor-driven handles</b>
1	4 238 45	Locking support for motor operators Cat.Nos 4 238 40/41/42/43. To be equipped with universal keylocks Cat.Nos 4 238 80/81/82/83 (p. 175)
1	4 238 46	Padlock for motor operators Cat.Nos 4 238 40/41/42/43