

DPX³ 250 HP

equipment and accessories (continued)



DPX³ 125/160/250 HP common auxiliaries and accessories



4 238 30

4 238 23



4 210 11

4 210 16

4 210 22

Pack	Cat.Nos	Connection accessories
1	4 238 34	Insulated shields (phase barriers) Set of 2 insulated shields for DPX ³ HP 125/250 3P
1	4 238 35	Set of 3 insulated shields for DPX ³ HP 125/250 4P
1	4 210 49	Padlock Padlock for locking in "open" position For DPX ³ 160/250 and DPX ³ 125/250 HP
		Cage terminals For Cu/Al cables, 1 x 120 mm ² for flexible cables and 1 x 150 mm ² for rigid cable
1	4 238 30	Set of 3 terminals for DPX ³ 250 HP 3P
1	4 238 31	Set of 4 terminals for DPX ³ 250 HP 4P
		Sealable terminal shields (for front terminals)
1	4 238 23	For DPX ³ 250 HP 3P
1	4 238 24	For DPX ³ 250 HP 4P
		Spreaders For incoming bars or cable lugs
1	6 250 14	Set of 3 spreaders for DPX ³ 250 HP 3P
1	6 250 18	Set of 4 spreaders for DPX ³ 250 HP 4P
		Rear terminals Flat swivel terminals Used to convert a fixed version with front terminals to a fixed version with rear terminals
1	4 238 21	Set of 3 rear terminals for DPX ³ 250 HP 3P
1	4 238 22	Set of 4 rear terminals for DPX ³ 250 HP 4P
		Universal key locks for DPX³ 125/160/250 HP and DPX³ 630/1600 Allow locking of rotary handles, draw-out mechanisms or motor-driven handles. To be used in combination with locking accessories Cat.Nos 4 228 06/07/08/09/10 (p. 179, 180 and 183) and 4 238 04/05/45/46/62/63 (p. 169 and 174)
1	4 238 80	Key barrel and flat key with random mapping
1	4 238 81	Key barrel and flat key with fixed mapping EL43525
1	4 238 82	Key barrel and flat key with fixed mapping EL43363
1	4 238 83	Key barrel and star key with random mapping

Pack	Cat.Nos	Auxiliary contact or fault signal	
1	4 210 11	Auxiliary contact or fault signalling contact	
		Shunt releases Allow remote tripping of a DPX ³ /DPX ³ -I 160/250 and DPX ³ /DPX ³ -I 125/160/250 HP	
1	4 210 12	12 V \sim /=	
1	4 210 13	24 V \sim /=	
1	4 210 14	48 V \sim /=	
1	4 210 15	110-130 V \sim	
1	4 210 16	200-277 V \sim	
1	4 210 17	380-480 V \sim	
		Undervoltage releases Allow remote tripping of a DPX ³ /DPX ³ -I 160/250 and DPX ³ /DPX ³ -I 125/160/250 HP	
1	4 210 18	12 V \sim /=	
1	4 210 19	24 V \sim /=	
1	4 210 20	48 V \sim /=	
1	4 210 21	110-130 V \sim /=	
1	4 210 22	200-240 V \sim	
1	4 210 23	277 V \sim	
1	4 210 24	380-415 V \sim	
1	4 210 25	440-480 V \sim	
		Time lag (800 ms) undervoltage release Allow remote tripping of a DPX ³ /DPX ³ -I 160/250 and DPX ³ /DPX ³ -I 125/160/250 HP Prevents false tripping in the event of power supply microbreaks	
		Time-lag modules	
1	0 261 90	230 V \sim	Number of modules 3
1	0 261 91	400 V \sim	3
		Release To be equipped with a time-lag module Cat.Nos 0 261 90/91	
1	4 210 98	For DPX ³ /DPX ³ -I 160/250 and DPX ³ /DPX ³ -I 125/160/250 HP	