

# DPX<sup>3</sup> magnetic release only

MCCBs from 16 to 1250 A for motor protection (continued)



4 239 33



4 239 45

Dimensions p. 191-192 and 194-197

Moulded case MCCBs for switching, control isolation and protection of three-phase motors  
 Can be fitted with auxiliaries (p. 175 and 184)  
 Supplied with: screws for connections, fixing screws and insulated shields (phase barriers)  
 Conform to IEC 60947-2

Pack	Cat.Nos		DPX <sup>3</sup> 250 HP
			Magnetic adjustable from 6 to 14 In Can be mounted on plate in XL <sup>3</sup> and XL <sup>3</sup> S cabinets and enclosures
			<b>Breaking capacity Icu 36 kA (400 V~)</b>
	3P	4P	In (A)
1	4 239 01	4 239 13	6.3
1	4 239 02	4 239 14	12.5
1	4 239 03	4 239 15	25
1	4 239 04	4 239 16	32
1	4 239 05	4 239 17	50
1	4 239 06	4 239 18	80
1	4 239 07	4 239 19	100
1	4 239 08	4 239 20	160
1	4 239 09	4 239 21	220
			<b>Breaking capacity Icu 50 kA (400 V~)</b>
1	4 239 25	4 239 37	6.3
1	4 239 26	4 239 38	12.5
1	4 239 27	4 239 39	25
1	4 239 28	4 239 40	32
1	4 239 29	4 239 41	50
1	4 239 30	4 239 42	80
1	4 239 31	4 239 43	100
1	4 239 32	4 239 44	160
1	4 239 33	4 239 45	220
			<b>Breaking capacity Icu 70 kA (400 V~)</b>
1	4 239 49	4 239 61	6.3
1	4 239 50	4 239 62	12.5
1	4 239 51	4 239 63	25
1	4 239 52	4 239 64	32
1	4 239 53	4 239 65	50
1	4 239 54	4 239 66	80
1	4 239 55	4 239 67	100
1	4 239 56	4 239 68	160
1	4 239 57	4 239 69	220
			<b>Breaking capacity Icu 100 kA (400 V~)</b>
1	4 239 73	4 239 85	6.3
1	4 239 74	4 239 86	12.5
1	4 239 75	4 239 87	25
1	4 239 76	4 239 88	32
1	4 239 77	4 239 89	50
1	4 239 78	4 239 90	80
1	4 239 79	4 239 91	100
1	4 239 80	4 239 92	160
1	4 239 81	4 239 93	220

Pack	Cat.Nos		DPX <sup>3</sup> 630
			Magnetic adjustable up to 10 In Can be mounted on plate in XL <sup>3</sup> and XL <sup>3</sup> S cabinets and enclosures
			<b>Breaking capacity Icu 36 kA (400 V~)</b>
	3P	4P	In (A)
1	4 226 08		320 with electronic release
1	4 225 98	4 226 16	400
1	4 226 09		400 with electronic release
1	4 225 99		500
1	4 226 00	4 226 17	630
			<b>Breaking capacity Icu 70 kA (400 V~)</b>
1	4 226 10		320 with electronic release
1	4 226 01	4 226 18	400
1	4 226 11		400 with electronic release
1	4 226 02		500
1	4 226 03	4 226 19	630
			<b>DPX<sup>3</sup> 1600</b>
			Magnetic adjustable up to 10 In Can be mounted on plate in XL <sup>3</sup> and XL <sup>3</sup> S cabinets and enclosures
			<b>Breaking capacity Icu 50 kA (400 V~)</b>
	3P	4P	In (A)
1	4 226 04	4 226 12	800
1	4 226 05	4 226 13	1000
			<b>Breaking capacity Icu 70 kA (400 V~)</b>
1	4 226 06	4 226 14	800
1	4 226 07	4 226 15	1000