

Trip free switches DMX³-I 1600

from 630 A to 1600 A



DMX³ 1600 / DMX³-I 1600 old range

selection table



0 282 64

Dimensions p. 226-227

Conform to IEC 60947-3

Pack	Cat.Nos		Fixed version
	JANUARY 2024		Supplied with: - 1 auxiliary contact: NO/NC - door sealing
	Frame 1600		
	3P	4P	In (A)
1	0 282 60	0 282 65	630
1	0 282 61	0 282 66	800
1	0 282 62	0 282 67	1000
1	0 282 63	0 282 68	1250
1	0 282 64	0 282 69	1600
			Draw-out version
	JANUARY 2024		Supplied with: - 1 auxiliary contact: NO/NC - door sealing To be installed on a draw-out base Cat.No 0 281 53 or 0 281 54 (p. 212)
	Frame 1600		
	3P	4P	In (A)
1	0 284 90	0 284 95	630
1	0 284 91	0 284 96	800
1	0 284 92	0 284 97	1000
1	0 284 93	0 284 98	1250
1	0 284 94	0 284 99	1600

DMX ³ 1600		ACBs TO BE EQUIPPED WITH MP4 PROTECTION UNITS			
Breaking capacity Icu (kA)	In (A)	Fixed version		Draw-out version	
		3P	4P	3P	4P
42 kA	630	0 280 00	0 280 06	0 280 71	0 280 76
	800	0 280 01	0 280 07	0 280 72	0 280 77
	1000	0 280 02	0 280 08	0 280 73	0 280 78
	1250	0 280 03	0 280 09	0 280 74	0 280 79
	1600	0 280 04	0 280 10	0 280 75	0 280 80
50 kA	630	0 280 24	0 280 30	0 280 81	0 280 86
	800	0 280 25	0 280 31	0 280 82	0 280 87
	1000	0 280 26	0 280 32	0 280 83	0 280 88
	1250	0 280 27	0 280 33	0 280 84	0 280 89
	1600	0 280 28	0 280 34	0 280 85	0 280 90
Draw-out base		-	-	0 281 53	0 281 54
MP4 protection units	LI	0 281 64			
	LSI	0 281 65			
	LSIg	0 281 66			
Communication option for MP4 protection units					0 281 70
External auxiliary power supply (input 230 V~)					0 281 72
Programmable output option for MP4 protection units					0 281 99
External neutral for DMX³ 1600					0 281 71
DMX³-I 1600		TRIP FREE SWITCHES			
	In (A)	Fixed version		Draw-out version	
		3P	4P	3P	4P
	1000	0 280 50	0 280 56	0 280 47	0 280 65
	1250	0 280 51	0 280 57	0 280 53	0 280 91
	1600	0 280 52	0 280 58	0 280 59	0 280 92
	Draw-out base	-	-	0 281 53	0 281 54