

DPX™ -IS 630 isolating switches

400 A to 630 A



0 266 62



0 266 70



0 262 50

Dimensions **p. 251**
 Electrical characteristics **p. 254**

Isolating switches for on-load circuit breaking by visible isolation and positive action of the contacts
 Padlock integrated in the handle
 Supplied with terminal shields, and cage terminals
 Conform to IEC 60947-3
 Category of use AC 23 A
 Accept electrical auxiliaries (p. 252)
 Can be mounted on plate in XL³ and XL³ S enclosures

Pack	Cat.Nos	DPX-IS with release
		Can be associated with a residual current relay with separate coil (p. 185), supplied without shunt trip
		Front handle
1	3P 4P 0 266 72 0 266 74	400 A
1	0 266 73 0 266 75	630 A
		Right-hand side handle
1	0 266 76 0 266 78	400 A
1	0 266 77 0 266 79	630 A
		Left-hand side handle
1	0 266 80 0 266 82	400 A
1	0 266 81 0 266 83	630 A
		DPX-IS without release
		Front handle
1	3P 4P 0 266 60 0 266 62	400 A
1	0 266 61 0 266 63	630 A
		Right-hand side handle
1	0 266 64 0 266 66	400 A
1	0 266 65 0 266 67	630 A
		Left-hand side handle
1	0 266 68 0 266 70	400 A
1	0 266 69 0 266 71	630 A
		Rotary handles
		Direct for emergency use
1	0 266 89	For mounting instead of standard handle
1	0 266 90	Front and right-hand side handle Left-hand side handle
		Vari-depth handle IP 55
		Comprising: connecting rod, bracket, self-adhesive drilling template, fixing accessories (seal to maintain the IP protection up to IP 55, door lock mechanism)
1	0 266 86	For front and side handle device
1	0 266 87	For front and side handle device for emergency use
		To be ordered with Cat.Nos 0 266 89 or 0 266 90

Pack	Cat.Nos	Accessories
		Cage terminals
1	0 262 50	Set of 4 terminals for cable 300 mm ² max. (rigid) or 240 mm ² max. (flexible)
1	0 262 51	Set of 4 high-capacity terminals for cable 2 x 240 mm ² (rigid) or 2 x 185 mm ² (flexible)
		Spreaders
1	3P 4P 0 262 48 0 262 49	Set of incoming and outgoing spreaders
		Rear terminals
		Used to convert the fixed version with front terminals to the fixed version with rear terminals
1	0 263 52 0 263 53	Set of incoming and outgoing flat rear terminals
		Sealable terminal shields
1	0 262 45	Set of 2
		Padlock
1	0 266 97	For locking mechanism in open position Padlock with flat key N° ABA90GEL6149