

# HRC cartridge fuses



Technical characteristics p. 263-264

Pack	Cat.Nos.		<b>Cylindrical type gG</b>		
	Conform to EN 60269-1, IEC 60269-1 and 2				
	<b>8 x 32 (previously 8.5 x 31.5)</b>				
	Without indicator	With indicator	Rating (Amps)	Voltage ~ (Volts)	Rupture capacity (Amps)
10	0 123 01		1	400	20000
10	0 123 02	0 124 02	2		
10	0 123 04	0 124 04	4		
10	0 123 06	0 124 06	6		
10	0 123 10		10		
10		0 124 10	10		
10	0 123 16	0 124 16	16		
	<b>10 x 38 HRC</b>				
	Without indicator	With indicator	Rating (Amps)	500	100000
10	0 133 94		0.5		
10	0 133 01		1		
10	0 133 02	0 134 02	2		
10	0 133 04	0 134 04	4		
10	0 133 06	0 134 06	6		
10	0 133 08	0 134 08	8		
10	0 133 10	0 134 10	10		
10	0 133 16	0 134 16	16		
10	0 133 20	0 134 20	20		
10	0 133 25	0 134 25	25		
	<b>14 x 51 HRC</b>				
	Without striker	With striker	Rating (Amps)	500	100000
10	0 143 06		6		
10	0 143 10		10		
10	0 143 16	0 145 16	16		
10	0 143 20	0 145 20	20		
10	0 143 25	0 145 25	25		
10	0 143 32	0 145 32	32		
10	0 143 40	0 145 40	40		
10	0 143 50	0 145 50	50		
	<b>22 x 58 HRC</b>				
	Without striker	With striker	Rating (Amps)	500	100000
10	0 153 16		16		
10	0 153 20		20		
10	0 153 25		25		
10	0 153 32		32		
10	0 153 40		40		
10	0 153 50	0 155 50	50		
10	0 153 63	0 155 63	63		
10	0 153 80	0 155 80	80		
10	0 153 96	0 155 96	100		
10	0 153 97 <sup>1</sup>	0 155 97 <sup>1</sup>	125		

Pack	Cat.Nos.		<b>Cylindrical type aM (motor rated)</b>		
	Conform to EN 60269-1, IEC 60269-1 and 2				
	<b>8 x 32 (previously 8.5 x 31.5)</b>				
	Without indicator		Rating (Amps)	Voltage ~ (Volts)	Rupture capacity (Amps)
10	0 120 04		4	400	20000
10	0 120 06		6		
10	0 120 08		8		
10	0 120 10		10		
	<b>10 x 38 HRC</b>				
	Without indicator		Rating (Amps)	500	100000
10	0 130 95		0.50		
10	0 130 01		1		
10	0 130 02		2		
10	0 130 04		4		
10	0 130 06		6		
10	0 130 08		8		
10	0 130 10		10		
10	0 130 12		12		
10	0 130 16		16		
10	0 130 20		20		
10	0 130 25		25		
	<b>14 x 51 HRC</b>				
	Without striker	With striker	Rating (Amps)	500	100000
10		0 141 02	2		
10		0 141 04	4		
10		0 141 06	6		
10		0 141 08	8		
10	0 140 10	0 141 10	10		
10	0 140 12	0 141 12	12		
10	0 140 16	0 141 16	16		
10	0 140 20	0 141 20	20		
10	0 140 25	0 141 25	25		
10	0 140 32	0 141 32	32		
10	0 140 40	0 141 40	40		
10	0 140 50 <sup>1</sup>	0 141 50 <sup>1</sup>	50		
	<b>22 x 58 HRC</b>				
	Without striker	With striker	Rating (Amps)	500	100000
10	0 150 25	0 151 25	25		
10	0 150 32	0 151 32	32		
10	0 150 40	0 151 40	40		
10	0 150 50	0 151 50	50		
10	0 150 63	0 151 63	63		
10	0 150 80	0 151 80	80		
10	0 150 96	0 151 96	100		
10	0 150 97 <sup>1</sup>	0 151 97 <sup>1</sup>	125		
	<b>Neutral links</b>				
10	0 123 00		8 x 32 (previously 8.5 x 31.5)		
10	0 133 00		10 x 38		
10	0 143 00		14 x 51		
10	0 153 00		22 x 58		

1: Overrating not described by standards