

Practibox S

flush-mounting cabinets for dry partitions from 4 to 72 modules



1 340 24



1 340 34



1 350 21



1 350 23

Technical characteristics p. 315

Allows to achieve assemblies conform to IEC 61439-3
IP40 IK07
Class II
Plastic material
Supplied with door
For dry partitions
850° fireproof flush-mounting plastic boxes

Pack	Cat.Nos		Number of rows	Number of modules per row	Total number of modules	Height (mm)	Width (mm)	Depth (mm)
	White door	Smoked Transparent door						
1	1 340 24	1 340 34	1	4	4	215	184	100
1	1 340 28	1 340 38	1	8	8	225	256	100
1	1 350 21	1 350 31	1	12	12	235	328	102
1	1 350 22	1 350 32	2	12	24	385	328	103
1	1 350 23	1 350 33	3	12	36	535	328	103
1	1 350 24	1 350 34	4	12	48	765	328	103
1	1 370 26	1 370 36	1	18	18	235	436	102
1	1 370 27	1 370 37	2	18	36	385	436	103
1	1 370 28	1 370 38	3	18	54	615	436	103
1	1 370 29	1 370 39	4	18	72	765	436	103
1	1 370 25	1 370 35	1	22	22	235	508	102

Cabinets supplied without terminal blocks

Pack	Cat.Nos		Number of rows	Number of modules per row	Total number of modules	Height (mm)	Width (mm)	Depth (mm)
	White door	Smoked Transparent door						
1	1 340 64	1 340 74	1	4	4	215	184	100
1	1 340 68	1 340 78	1	8	8	225	256	100
1	1 350 61	1 350 71	1	12	12	235	328	102
1	1 350 62	1 350 72	2	12	24	385	328	103
1	1 350 63	1 350 73	3	12	36	535	328	103
1	1 350 64	1 350 74	4	12	48	765	328	103
1	1 370 66	1 370 76	1	18	18	235	436	102
1	1 370 67	1 370 77	2	18	36	385	436	103
1	1 370 68	1 370 78	3	18	54	615	436	103
1	1 370 69	1 370 79	4	18	72	765	436	103
1	1 370 65	1 370 75	1	22	22	235	508	102

Cabinets supplied with earth terminal blocks

Pack	Cat.Nos		Number of rows	Number of modules per row	Total number of modules	Height (mm)	Width (mm)	Depth (mm)
	White door	Smoked Transparent door						
1	1 341 64	1 341 74	1	4	4	215	184	100
1	1 341 68	1 341 78	1	8	8	225	256	100
1	1 351 61	1 351 71	1	12	12	235	328	102
1	1 351 62	1 351 72	2	12	24	385	328	103
1	1 351 63	1 351 73	3	12	36	535	328	103
1	1 351 64	1 351 74	4	12	48	765	328	103
1	1 371 66	1 371 76	1	18	18	235	436	102
1	1 371 67	1 371 77	2	18	36	385	436	103
1	1 371 68	1 371 78	3	18	54	615	436	103
1	1 371 69	1 371 79	4	18	72	765	436	103
1	1 371 65	1 371 75	1	22	22	235	508	102

Cabinets supplied with earth and neutral terminal blocks

Practibox S

accessories



1 348 13



4 018 56

Pack	Cat.Nos	Earth terminal blocks
1	1 348 00	Brass terminal block with isolated support Conform to IEC 60998-2-1/2-2 For 4 modules cabinets 1 x (2x16 ² + 2x10 ²); ICC : 6 kA
1	1 348 01	For 8 modules cabinets 1 x (3x16 ² + 3x10 ²); ICC : 6 kA
1	1 348 02	For 12 modules flush-mounting cabinets 1 x (12x16 ² + 12x10 ²); ICC : 6 kA
1	1 348 03	For 12 modules surface-mounting cabinets 1 x (12x16 ² + 12x10 ²); ICC : 6 kA
1	1 348 04	For 1 row 18 modules flush-mounting cabinets 1 x (1x25 ² + 12x16 ²); ICC : 10 kA
1	1 348 05	For 18 modules surface-mounting cabinets and 2 to 4 rows flush-mounting cabinets 1 x (1x25 ² + 26x16 ²); ICC : 10 kA
1	1 348 10	Earth and neutral terminal block Brass terminal block with isolated support Conform to IEC 60998-2-1/2-2 For 4 modules cabinets 2 x (2x16 ² + 2x10 ²); ICC : 6 kA
1	1 348 11	For 8 modules cabinets 2 x (3x16 ² + 3x10 ²); ICC : 6 kA
1	1 348 12	For 12 modules flush-mounting cabinets 2 x (12x16 ² + 12x10 ²); ICC : 6 kA
1	1 348 13	For 12 modules surface-mounting cabinets 2 x (12x16 ² + 12x10 ²); ICC : 6 kA
1	1 348 14	For 1 row 18 modules flush-mounting cabinets 2 x (1x25 ² + 12x16 ²); ICC : 10 kA
1	1 348 15	For 18 modules surface-mounting cabinets and 2 to 4 rows flush-mounting cabinets 2 x (1x25 ² + 26x16 ²); ICC : 10 kA
1	1 348 16	For 22 modules cabinets 2 x (1x25 ² + 12x16 ²); ICC : 10 kA
1	1 341 00	Accessories Key lock Can be mounted on all sizes of flush and surface-mounting enclosures
1	1 341 02	Horizontal and vertical joining kit for flush-mounting enclosure
1	4 018 56	Set of 4 wall fixing lugs for XL ³ 125 and Practibox S surface-mounting cabinets
20	0 016 60	Blanking plates Separable per module or 1/2 module 5 modules
10	0 016 62	13 modules
10	0 016 64	18 modules