

Flush-mounting cabinets Practibox³

from 8 to 72 modules



Technical characteristics p. 317

Class II
 IP 40 - IK 07 with door
 Self-extinguishing: resistance to incandescent wire 850 °C
 Conform to IEC 60670-24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439-3

Pack	Cat.Nos		Flush-mounting distribution cabinets				
			Box for masonry or dry partitions (with dry partitions kit Cat.No 4 017 24) Supplied with: - removable chassis with rails fitted - reversible door (door + faceplate for 1-row cabinets) - removable faceplates for each row (for 2, 3 and 4-row cabinets) - IP 2X screw terminal blocks - blanking plates (5 modules, separable per module or 1/2 module, for 2, 3 and 4-row cabinets) Spacing between rails 150 mm Door opening : 180° Can be equipped with lock and key n° 850 Cat.No 0 019 66				
			8/12 modules per row with transparent door				
			Flush-mounting box				
			Number of rows	Number of modules	Height (mm)	Width (mm)	Depth (mm)
1	4 017 01	4 017 51	1	8	186	232	80
1	4 017 02	4 017 52	1	12	222	304	80
1	4 017 03	4 017 53	2	24	372	304	85
1	4 017 04	4 017 54	3	36	522	304	85
			8/12 modules per row with white door RAL 9003				
1	4 017 11	4 017 61	1	8	186	232	80
1	4 017 12	4 017 62	1	12	222	304	80
1	4 017 13	4 017 63	2	24	372	304	85
1	4 017 14	4 017 64	3	36	522	304	85
			18 modules per row with transparent door				
1	4 017 06	4 017 56	1	18	248	436	85
1	4 017 07	4 017 57	2	36	456	436	85
1	4 017 08	4 017 58	3	54	606	436	91
1	4 017 09	4 017 59	4	72	756	436	91
			18 modules per row with white door RAL 9003				
1	4 017 16	4 017 66	1	18	248	436	85
1	4 017 17	4 017 67	2	36	456	436	85
1	4 017 18	4 017 68	3	54	606	436	91
1	4 017 19	4 017 69	4	72	756	436	91

Pack	Cat.Nos	Accessories
1	4 017 23	Horizontal or vertical joining kit For joining 2 cabinets when installed in masonry
1	4 017 24	Flush-mounting kit for dry partitions For installation of Practibox ³ cabinets in dry partitions
1	4 017 22	Horizontal partition for 18 modules per row cabinets For 2, 3 or 4-rows cabinets
1	4 017 25	Plain faceplate for 18 modules per row cabinets For 2, 3 or 4-rows cabinets Allow fitting of non-modular equipments such as control and signalling units
		Perforated plates for 18 modules per row cabinets To be used instead of the one rail when integrating non-modular products
1	4 017 26	For 2, 3 or 4-rows cabinets Height 150 mm
1	4 017 27	12x2 flat bar for IP 2X terminal blocks for 18 modules per row cabinets For 2, 3 or 4-rows cabinets Allow fitting of additional IP 2X terminal blocks
1	0 019 66	Key lock To be fitted on white or transparent doors, starting from 3 rows of 12 modules cabinets Supplied with key n° 850
		Blanking plates White RAL 9003 Separable per module or 1/2 module
20	0 016 60	5 modules
10	0 016 62	13 modules
10	0 016 64	18 modules

