

# XL<sup>3</sup> S 160 - 24 modules per row

“ready to use” metal distribution cabinets



3 372 04



3 372 24

Technical characteristics p. 325

Cabinets supplied with rails fitted (150 mm fixing centres) and full height faceplates  
 Doors and terminal blocks to be ordered separately  
 Take DPX<sup>3</sup> 160 and modular protection devices  
 Used to create assemblies certified IEC 61439-2 and -3  
 IP 40 with door  
 IP 30 without door  
 Cut-outs in top and bottom for feeding cables through  
 Can take Lina 25 ducting

## Pack Cat.Nos Surface-mounting 24-module cabinets

Pack	Cat.Nos	Faceplates and body: RAL 9003					
		No. of rows	No. of modules	Height (mm)	Width (mm)	Depth (mm)	
1	3 372 02	2	48	440	595	135	200 200
1	3 372 03	3	72	590	595	135	200 150 200
1	3 372 04	4	96	740	595	135	200 150 150 200
1	3 372 05	5	120	890	595	135	200 150 150 150 200
1	3 372 06	6	144	1040	595	135	200 150 150 150 150 200
1	3 372 07	7	168	1190	595	135	200 150 150 150 150 150 200
1	3 372 08	8	192	1340	595	135	200 150 150 150 150 150 150 200

## Pack Cat.Nos Flush-mounting 24-module cabinets

Pack	Cat.Nos	Supplied with fixing lugs Faceplates: RAL 9003					
		No. of rows	No. of modules	Height (mm)	Width (mm)	Depth (mm)	
1	3 372 22	2	48	512	667	138	200 200
1	3 372 23	3	72	662	667	138	200 150 200
1	3 372 24	4	96	812	667	138	200 150 150 200
1	3 372 25	5	120	962	667	138	200 150 150 150 200
1	3 372 26	6	144	1112	667	138	200 150 150 150 150 200
1	3 372 27	7	168	1262	667	138	200 150 150 150 150 150 200
1	3 372 28	8	192	1412	667	138	200 150 150 150 150 150 150 200