

XL³ S 160

equipment and accessories



3 372 54



3 372 64



3 372 74



3 372 84



0 203 99

Pack	Cat.Nos	Metal doors
		Supplied with handle Cat.No 3 397 10
		For cabinets with 24 modules per row
		For cabinet (no. of modules)
1	3 372 52	2 × 24
1	3 372 53	3 × 24
1	3 372 54	4 × 24
1	3 372 55	5 × 24
1	3 372 56	6 × 24
1	3 372 57	7 × 24
1	3 372 58	8 × 24
		For cabinets with 36 modules per row
1	3 372 64	4 × 36
1	3 372 65	5 × 36
1	3 372 66	6 × 36
1	3 372 67	7 × 36
1	3 372 68	8 × 36
		Glass doors
		For cabinets with 24 modules per row
		For cabinet (no. of modules)
1	3 372 72	2 × 24
1	3 372 73	3 × 24
1	3 372 74	4 × 24
1	3 372 75	5 × 24
1	3 372 76	6 × 24
1	3 372 77	7 × 24
1	3 372 78	8 × 24
		For cabinets with 36 modules per row
1	3 372 84	4 × 36
1	3 372 85	5 × 36
1	3 372 86	6 × 36
1	3 372 87	7 × 36
1	3 372 88	8 × 36
		Replacement handle for doors
1	3 397 10	Handle for XL ³ S 160 door
1	3 397 15	Locking handle no. 405 Supplied with a set of 2 keys
		Accessories
1	3 374 04	Joining kit For connecting two surface-mounting XL ³ S 160 cabinets vertically
1	3 374 00	Wall mounting lugs Set of 4 lugs for wall mounting
1	3 374 06	Fixing kit for hollow partition Kit for fixing XL ³ S 160 flush-mounting cabinets in hollow partitions
1	3 374 05	Fixing support for ducting Set of 2 supports
		Fixing plate and faceplate for DPX³ 160
1	3 374 10	For XL ³ S 160 cabinets with 24 modules per row
1	3 374 11	For XL ³ S 160 cabinets with 36 modules per row

Pack	Cat.Nos	Rail position adjustment kit for DPX ³ 160
1	3 374 07	For positioning the rail at the correct height to take DPX ³ 160 MCCBs For XL ³ S 160 cabinets with 24 and 36 modules per row
		Self-adhesive document holders for plans
		Open - RAL 7035
		External dimensions
		Height (mm) Width (mm)
20	0 365 80	235 340
20	0 365 81	165 260
		Internal dimensions
		Height (mm) Width (mm) Depth (mm)
		200 310 18
		130 230 18
		Closed - RAL 7035
1	0 365 82	Rigid, plastic, IP 50 Internal dimensions: 324 x 120 x 18 mm
		Transparent
10	0 097 99	Soft plastic, A4 - 305 x 220 mm
		Rail height spacer
1	3 382 40	Used to combine modular devices and DPX ³ 160/250 on the same row
1	3 382 41	Used to combine modular devices and DRX on the same rail
1	3 382 42	Used to combine DRX and DPX ³ 160/250 on the same rail
		White RAL 9003 blanking plates
20	0 016 60	5 modules. Separable into modules or half-modules
20	3 397 54	24 modules, untapped blanking panel which can be cut as required
		Clip-on holders for self-adhesive labels
		Supplied with sheet of labels for marking rows on faceplate
10	3 397 55	24 modules
10	3 397 56	36 modules
		Connection of protective conductors
		Additional brass bar
		For protective conductor. Fits using the lugs supplied with the cabinets
1	0 373 00	For 24-module width enclosure
1	3 397 57	For 36-module width enclosure
		Equipotential link conductor
1	3 397 53	Length 350 mm. Cross-section 6 mm ²