

XL³ S 630

distribution enclosures



3 375 81 + 3 382 00



3 375 82 + 3 382 00



3 375 83



3 375 20



3 378 68

Technical characteristics **p. 343**

Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately p. 341)

Doors and side panels to be ordered separately

Take protection devices up to 630 A

Used to create assemblies certified IEC 61439-2

IP 40 with door

IP 30 without door

Removable, separable top and bottom panels

Can take Lina 25 ducting and IP 55 Cabstop cable gland plates (p. 342)

Pack	Cat.Nos	Enclosures				
		16 modules wide				
		Faceplates: RAL 9003				
		Body: RAL 7016				
		Height (mm)		Width (mm)		Depth (mm)
		total	faceplate	total	usable	
1	3 375 21	824	750	454	350	249
1	3 375 31	974	900	454	350	249
1	3 375 41	1124	1050	454	350	249
1	3 375 51	1274	1200	454	350	249
1	3 375 61	1424	1350	454	350	249
1	3 375 71	1574	1500	454	350	249
1	3 375 81	1724	1650	454	350	249
1	3 375 91	1874	1800	454	350	249
1	3 376 01	2024	1950	454	350	249
1	3 376 11	2174	2100	454	350	249
1	3 376 21	2324	2250	454	350	249
		24 modules wide				
1	3 375 22	824	750	604	500	249
1	3 375 32	974	900	604	500	249
1	3 375 42	1124	1050	604	500	249
1	3 375 52	1274	1200	604	500	249
1	3 375 62	1424	1350	604	500	249
1	3 375 72	1574	1500	604	500	249
1	3 375 82	1724	1650	604	500	249
1	3 375 92	1874	1800	604	500	249
1	3 376 02	2024	1950	604	500	249
1	3 376 12	2174	2100	604	500	249
1	3 376 22	2324	2250	604	500	249
		36 modules wide				
1	3 375 23	824	750	804	700	249
1	3 375 33	974	900	804	700	249
1	3 375 43	1124	1050	804	700	249
1	3 375 53	1274	1200	804	700	249
1	3 375 63	1424	1350	804	700	249
1	3 375 73	1574	1500	804	700	249
1	3 375 83	1724	1650	804	700	249
1	3 375 93	1874	1800	804	700	249
1	3 376 03	2024	1950	804	700	249
1	3 376 13	2174	2100	804	700	249
1	3 376 23	2324	2250	804	700	249

Pack	Cat.Nos	Internal cable sleeves			
		Internal cable sleeve kits			
		For mounting on either the right or left inside XL ³ S 630 enclosures			
		Height (mm)		Depth (mm)	
		total	faceplate		
1	3 379 32	824	750	249	
1	3 379 33	974	900	249	
1	3 379 34	1124	1050	249	
1	3 379 35	1274	1200	249	
1	3 379 36	1424	1350	249	
1	3 379 37	1574	1500	249	
1	3 379 38	1724	1650	249	
1	3 379 39	1874	1800	249	
1	3 379 40	2024	1950	249	
1	3 379 41	2174	2100	249	
1	3 379 42	2324	2250	249	
		External cable sleeves			
		Side cable sleeves			
		Fitted on either the right or left of enclosures using joining kits Cat.Nos 3 379 49/50			
		Height (mm)		Width (mm)	Depth (mm)
		total	faceplate	total (mm)	
1	3 375 20	824	750	324	249
1	3 375 30	974	900	324	249
1	3 375 40	1124	1050	324	249
1	3 375 50	1274	1200	324	249
1	3 375 60	1424	1350	324	249
1	3 375 70	1574	1500	324	249
1	3 375 80	1724	1650	324	249
1	3 375 90	1874	1800	324	249
1	3 376 00	2024	1950	324	249
1	3 376 10	2174	2100	324	249
1	3 376 20	2324	2250	324	249
		Side panels			
		Set of 2 panels			
		For cabinets or cable sleeves with faceplate height (mm)			
1	3 378 62	750			
1	3 378 63	900			
1	3 378 64	1050			
1	3 378 65	1200			
1	3 378 66	1350			
1	3 378 67	1500			
1	3 378 68	1650			
1	3 378 69	1800			
1	3 378 70	1950			
1	3 378 71	2100			
1	3 378 72	2250			